

Run Capacitor Holder

In order to meet our customers' requirements for flexible solutions Danfoss has introduced a run capacitor holder for our "Energy-optimized" and "High Energy-optimized" compressor range. This optional part enables to fix the run capacitor for 220 V directly and earth-connected on the compressor shell, concentrating all electrical accessories on the compressor. This will save space in the machine compartment.

Technical features summary:

- saves space in the machine compartment
- integrated earth connection between compressor shell and capacitor clamp due to the special screw head
- concentration of all electrical accessories on the compressor

Availability:

- Status: running production
- Code numbers: run capacitor holder (**Fig. 1**) 117-0300
screw M4 x 8 PZD 2 (**Fig. 2**) 117-0301

Montagewinkel für Betriebskondensator

Auf Wunsch verschiedener Kunden bietet Danfoss jetzt für "energieoptimierte" und "hoch energieoptimierte" Verdichter einen Montagewinkel für den Betriebskondensator an. Dieses optionale Zubehörteil ermöglicht die Montage des 220V Betriebskondensators direkt, platzsparend und geerdet am Verdichter.

Technische Vorteile:

- spart Platz in der Verdichternische
- Betriebskondensator ist über Verdichtergehäuse durch speziellen Schraubenkopf geerdet
- Konzentration des elektrischen Zubehörs am Verdichter

Lieferbarkeit:

- Status: laufende Fertigung
- Bestellnummer: Montagewinkel (**Fig. 1**) 117-0300
Schraube M4 x 8 PZD 2 (**Fig. 2**) 117-0301

Montagebøjle til driftskondensator


For at imødekomme vore kunders ønsker, har Danfoss introduceret en montagebøjle til driftskondensatoren til "energioptimerede" og "højt energioptimerede" kompressorer. Med denne optionale part kan 220 V driftskondensatoren monteres pladsbesparende og jordforbundet direkte på kompressoren.

Tekniske features:


- sparer plads i kompressorummet
- kondensatoren bliver jordforbundet via kompressorhuset med det specielle skruehoved
- el-tilbehøret koncentrerer på kompressoren

Levering:

- Status: løbende produktion
- Kodenumre: montagebøjle (**Fig. 1**) 117-0300
skruer M4 x 8 PZD 2 (**Fig. 2**) 117-0301



run capacitor holder with screw



assembly sequence

Please also visit our web site:

www.danfoss.com/compressors

and have a look at our complete product range covering all your present and future applications, news and literature.

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



Danfoss Compressors GmbH

Mads-Clausen-Strasse 7
Postfach 1443, D-24939 Flensburg
Telefon: (0461) 4941-0
International +49 461 4941-0
Telefax: +49 461 44715
Telex: 227 43 dancom d
