



**60 Hz**  
**PRELIMINARY**



## **Medium temperature refrigeration**

**Scroll compressors 60 Hz - R404A / R134a / R22 / R507A**


## CODE NUMBERS

### Features


- ☑ Compressor range from 15,000 to 78,000 Btu/hr cooling capacity
  - ☑ Multi-refrigerant compressor suitable for R404A, R507A, R134a and R22
  - ☑ Suitable for operation down to 50°F condensing temperature for improved energy efficiency
  - ☑ Oil sight glass & schraeder connection for oil fill/drain
- ☑ Rubber mounting grommets
  - ☑ Brazed connectors
  - ☑ IP 22 electrical box
  - ☑ Optional rotolock fittings, crankcase heater, sound jacket

### Product range & technical specifications

Model	Product range					Sound power (dBA)	Net weight (lbs)	Oil charge (oz)	Dimensions in inch			
	Code 1	Code 2	Code 4	Code 7	Code 9				D	H	H1	H2
MLZ 015	●	●	●	●	●	68	67.0	36	6.50	16.26	9.84	14.92
MLZ 019	●	●	●	●	●	68	67.0	36				
MLZ 021	●	●	●	●	●	68	67.0	36				
MLZ 026	●	●	●	●	●	70	67.0	36				
MLZ 030	●	●	●	●	●	73	82.0	53	7.24	17.91	11.02	16.61
MLZ 038	●	●	●	●	●	74	82.0	53				
MLZ 045	●	●	●	●	●	74	87.0	53				
MLZ 048	●	●	●	●	●	75	87.0	53				
MLZ 058	●	●	●	●	●	77	97.0	90	7.24	21.10	14.53	20.04
MLZ 066	●	●	●	●	●	77	99.6	90	7.24	21.46	14.53	20.43
MLZ 076	●	●	●	●	●	77	99.6	90				



MLZ015 - 048



MLZ058 - 076





## The Danfoss product range for the refrigeration and air conditioning industry

Danfoss Refrigeration & Air Conditioning is a worldwide manufacturer with a leading position in industrial, commercial and supermarket refrigeration as well as air conditioning and climate solutions.

We focus on our core business of making quality products, components and systems that enhance performance and reduce total life cycle costs – the key to major savings.



*Controls for Commercial Refrigeration*



*Controls for Industrial Refrigeration*



*Electronic Controls & Sensors*



*Industrial Automation*



*Household Compressors*



*Commercial Compressors*



*Sub-Assemblies*



*Thermostats*



*Brazen plate heat exchanger*

We are offering a single source for one of the widest ranges of innovative refrigeration and air conditioning components and systems in the world. And, we back technical solutions with business solution to help your company reduce costs, streamline processes and achieve your business goals.

**Danfoss A/S • [www.danfoss.com](http://www.danfoss.com)**

Danfoss Refrigeration & Air-Conditioning Division, [www.danfoss.com/North\\_America](http://www.danfoss.com/North_America)

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.