

additional informations:
 filter colour : zink plated steel
 filter weight : 26,5kg

label:




VLT MCC 101 sine wave FILTER
 www.danfoss.com Danfoss A/S 5450 Nordborg, Denmark

T/C: MCC101 A28RTERRB S/N: 000188-188
 P/N: 130B4112
 S/N: 325800 - 506094 / Imp: 100749
 50/250V ~ 50/60Hz / Imp: 100749
 Chassidimp00 Temp: 45°C/113°F
 130B4112003551-188

MADE IN GERMANY
 L=4,0mm
 C=6,0mm
 S=4,0mm
 P=5,0mm
 W=150mm
 Weight: 26,5kg
 Tightening torque
 terminal 2: 2,5Nm
 50/250V
 EN 60556

Use only with a Type 1 or type 2 SPD, semiconductor control device

E 210222
 Ind Control: 1101
 B 1002050
 U: U-requirements
 EN 60556




2pcs earth screws M6x16
 (with lockwasher and washer)

e 04.05.16	Schr./Fie.	typeable updated.	Danfoss Postaddress included
d 10.11.14	Schr./Fie.	typeable updated	
c 13.08.13	KOR/Fie.	cabling updated	
b 14.01.13	Schr./KOR	typeable updated, accessories added	
a 01.10.10	KOR/Lauer	approval added	




Dimensions toleranced according to ISO 2768-m			
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30
m (middle)	±0.1	±0.1	±0.2

drawn	04.06.10	Kornrau	Kornrau	scale	1:4
checked	04.06.10	Bremer	Bremer	format	A4
date		name		signature	

Dimensions B 1002050			
sine wave filter 690V 28A - IP00			
order number	130B4112	drawing number	Z791004010
Please observe protection clause to ISO 16016			
modi.	e	sheet	1/2



included accessories
(screen connection plate)



- e|04.05.16| Schr./Fie. | typeable updated, Danfoss Postaddress included
- d|10.11.14| Schr./Fie. | typeable updated
- c|13.08.13| KOR/Fie. | cabling updated
- b|14.01.13| Schr./KOR | typeable updated, accessories added
- a|01.10.10| KOR/Lauer | approval added

date name amendment

Dimensions toleranced according to ISO 2768-m

Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	04.06.10	Kornau	Kornau	scale	1:4
checked	04.06.10	Bremer	Bremer	format	A4
	date	name	signature		

Dimensions B 1002050

sine wave filter 690V 28A - IP00

order number	130B4112	drawing number	Z791004010	modi.	e	sheet	2/2
--------------	----------	----------------	------------	-------	---	-------	-----

Please observe protection clause to ISO 16016

