

additional informations:
 filter colour : RAL7001
 filter weight : 49kg
 cable clamp : 2x 130B4045

50mm² terminal

label:

VLT MCC-101 sine wave FILTER
 www.danfoss.com

TTC MCC-01MARKTTE208
 PN: 130B4115
 3x 525-690V - 50/60 Hz (max. 100 A)
 3x 45A @ 50 Hz 42% @ 60 Hz 35A @ 100 Hz
 Chassis size: 2U form 253x118 mm





SIN 000188-186
 L=25mmH
 Q=15A
 Filter: S&KZ
 Weight: 49kg
 Tipingering for use only CU

Use only with a Type 1 or type 2 SPD overvoltage control device

E: 219022 B: 10020511 FA: NR: 10001000
 Fil: ContEd: HED1 Star: manual for UL-requirements

EN 61558

UL
 CE



d) 04.05.16 Schr./File. typeable updated, Danfoss Postaddress included
 c) 10.11.14 Schr./File. typeable updated
 b) 14.01.13 Schr./Kar. typeable updated
 a) 01.10.10 KOR/Lauer approval added

drawn	04.06.10	Kornrau	Kornrau	scale	1:5
checked	04.06.10	Bremer	Bremer	formate	A4
date			signature		





Dimensions B 1002051.1
 sine wave filter 690V 45A - IP20

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

Dimensions toleranced according to ISO 2768-m	
Tolerance class	0.5 to 3
m (middle)	±0.1

order number	130B4115	drawing number	Z791004035	modi.	d	sheet	1/2
Please observe protection clause to ISO 16016							

included accessories
(screen connection plate)



d|04.05.16 Schr./Fle. typeable updated; Danfoss Postaddress included
 c|10.11.14 Schr./Fle. typeable updated
 b|14.01.13 Schr./Kor. typeable updated
 a|01.10.10 KOR/Lauer approval added
 date name amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	04.06.10	Kornau	Kornau	scale	1:5
checked	04.06.10	Bremer	Bremer	format	A4
	date	name	signature		

Dimensions B 1002051.1

sine wave filter 690V 45A – IP20

order number 130B4115 drawing number Z791004035 mod. d sheet 2/2

Please observe protection clause to ISO 16016

