

Ordering no.: 176F4712

FC 302 N160 T7 + FC 202 N200 T7 + FC 102 N200 T7

FC 302 N200 T7 + FC 202 N250 T7 + FC 102 N250 T7

FC 302 N250 T7 + FC 202 N315 T7 + FC 102 N315 T7

FC 302 N315 T7 + FC 202 N400 T7 + FC 102 N400 T7

Description	Code no.	Qty.
Control Card, FC 302 with safe stop	130B1109	1
Control Card, FC 102 with safe stop	130B1150	1
Control Card, FC 202 with safe stop	130B1167	1
Heatsink Fan	176F3164	1
Mixing Fan	176F3165	1
IP20 Top Fan	176F3167	1
IP21/54 Door Fan	176F3169	1
Mains Fuse	176F3173	3
IGBT Gate Drive Cable	176F3176	3
IGBT Temperature Cable	176F3178	1
Brake IGBT Gate Drive Cable	176F3180	1
SCR Gate Drive Cable	176F3336	1
Door Fan Filter	176F3353	1
Brake IGBT Module	176F3367	1
Door Vent Kit	176F3375	1
Current Scaling	176F3413	1
Current Scaling	176F3414	1
Current Scaling	176F3415	1
Current Scaling	176F3416	1
Balance/HF Card	176F3419	1
IGBT Module	176F3424	3
IGBT Module	176F3425	3
SCR/Diode	176F3426	3
Snubber Capacitor	176F3427	3
DC Bus Capacitor	176F3428	12
Bus Bar Assembly	176F3432	1
Power Card Rugged NO 200kW 525-690V	176F3499	1
Power Card Rugged NO 250kW 525-690V	176F3500	1
Power Card Rugged NO 315kW 525-690V	176F3501	1
Power Card Rugged NO 400kW 525-690V	176F3502	1
Gate Drive Card Rugged NO 75-400kW 690V	176F3516	1
Inrush Card Rugged NO 75-400kW 690V	176F3518	1
Current Sensor	176F8342	3
Current Sensor	176F8343	3
Cable Control Card to Power Card D2h/D4h	176F3319	1
SCR/Diode	176F8530	3
CONTAINER FOR SERVICE KIT	175z2908	1
Current Sensor 300A	176F6515	3
Current Sensor 500A	176F6447	3
Control Card MKII with safe stop for FC-302/FC3	134B1726	1
Control Card MKII with safe stop for FC-102	134B1729	1
Control Card MKII with safe stop for FC-202	134B1731	1
DC Bus CAP T7 drive Single in Housing	176F6635	12
Bus Bar Assembly CAP Bank 690V D1h/D3h	176F6766	1
Bus Bar Assembly CAP Bank 690V D2h/D4h	176F6768	1
Tool capacitor removal installation	176F6692	1