







12 11 10 9 8 7 6 5 4 3 2 1

Type	Value
IP Class	IP20
UL Type	Open
Enclosure Colour	RAL 7001
Frame Size	P2AX8i



Dimension [mm]	Tolerances			parts in series	folded parts
	<250	250>x>800	>800		
Tolerance [mm]	+/-1	+/-2.5	+/-4	+/-2.5	+/-2.5




A (2 : 3)

B (2 : 3)

C (2 : 3)

ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		Projection	Scale 1:3
Gezeichnet	DATUM	Name	
Kontrolliert	2022-02-25	FR	AHF P2AX8i IP20
None			
136b3117			REV 002
Status	Änderungen	DATUM	Name
Sheet 1 of 4			Size A1

12 11 10 9 8 7 6 5 4 3 2 1





ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			1:4	
		DATUM	Name	
		Gezeichnet 2022-02-25	FR	
		Kontrolliert		AHF P2AX8i IP20
		Notiz		
				136b3117
				REV 002
				Size A1
Status	Änderungen	DATUM	Name	Sheet 2 of 4

Included Accessories (premounted)				
Pos.	Pcs.	Description	Type	Torque
1	1	strain relief X1/X2	-	-
2	4	screw	M5x10 HX4	5Nm
3	1	strain relief X3/X4	-	-
4	2	screw	M5x6 HX4	5Nm

A/B Temperature 2,5mm²
Torque: 0.8Nm Tool Slot 0.5x3.0

X3/4 Capacitor Disconnect 95mm²
Torque: 18Nm Tool S6

X3 . 1 X4 . 1 X3 . 2 X4 . 2 X3 . 3 X4 . 3




X1.1 X1.2 X1.3 X2.1 X2.2 X2.3

X1 Mains 300mm²
Torque: 50m Tool SW24

X2 Drive 300mm²
Torque: 50Nm Tool SW24

Scale (2 : 3)



Scale (1 : 5)

ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			1:3	
Gezeichnet	DATUM	Name		
Kontrolliert	2022-02-25	FR		
None			AHF P2AX8i IP20	
			136b3117	REV 002
Status	Änderungen	DATUM	Name	Size A1
				Sheet 3 of 4

Product Label (95x50mm)



Packaging Label (90x50mm)



OF7P2	Identification	Voltage	Output Current	Input Current	Grid frequency	THDI	Ploss	Weight	Frame	UL mark	Revcon part number
P/N	T/C	[V]	[A]	[A]	[Hz]	[%]	[W]	[kg]	-	-	ZZZZZZZZ
132N6513	OF7P2-S-AF-46-291A-060-05-T1-E20	460/400	291/304	291/304	60	5	1664	221	X8	x	25040034
132N6817	OF7P2-S-AF-40-325A-050-05-T1-E20	-/400	-/325	-/325	50	5	1385	221	X8	-	25040016

ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			3:1	
		DATUM	Name	
		Gezeichnet 2022-02-25	FR	
		Kontrolliert		AHF P2AX8i IP20
		None		
				136b3117
Status	Änderungen	DATUM	Name	REV 002 Size AT
		3		Sheet 4 of 4