



# 1 Danfoss Power Solutions HWD DM1000 70312394 Revision History

This file contains important supplementary and late-breaking information that may not appear in the main product documentation. We recommend that you read this file in its entirety.

## 2 Version DM1000 70312394v241 19.11r01 (Nov 2019)

### 2.1 What is New

- No new items.

### 2.2 Fixes to the HWD

- Revision History document - Section 2 is not updated [BUG-109977]
- Widget Stacking Order is Wrong [BUG-172232]
- Successive opening of PDF file sometimes fails [BUG-174078]
- PDF viewer horizontal scrolling issue [BUG-172449]
- Copy to /home/p1user/media returns incorrect DirAPI.OperationStatus [BUG-168579]
- DirAPI.OperationStatus returns undefined status 65535 [BUG-168181]
- PDF Viewer can not open file from USB drive [BUG-168696]
- GNSS SatellitesUsed reports 0 [BUG-164870]
- VCAN channel stall due to CAN23 BUS-OFF [BUG-166572]
- DirAPI copy data to new created folder on USB host fails [BUG-166302]
- p1user/media folder not loaded/not accessible [BUG-167311]
- DirAPI copy of file > 70MB causes system restart [BUG-163648]
- Dir API Copy/Delete Issues (Incorrect Access Rights) [BUG-160006]
- Downgrade of system not functional (download not completed) [BUG-162245]
- Rotated image is cropped in widget [BUG-165131]
- Download ROP failed [BUG-165159]
- CAN23 baudrate change fails [BUG-135022]
- DM1x00 Long Boot-up time [BUG-138314]
- Board goes to boot loader mode after reboot/download [BUG-162260]
- DM1x00 touchscreen not functional [BUG-159933]

- Bluetooth pairing mismatch [BUG-147754]
- USB autoconfig in recovery not transferred to normal mode [BUG-158661]
- M2M application download failed [BUG-138398]
- M2M cannot be initialized with empty string DoIP PWD [BUG-160009]
- HWD Revision History document is not generated [BUG-19364]
- Cannot change USB DHCPService data in recovery mode [BUG-157932]
- Text area is black when string is empty [BUG-159258]
- CAN not recover from BUS-OFF [BUG-129988]
- MultipleROP test failed [BUG-158267]
- DirAPI Copy problem (Path do not exist) [BUG-153685]
- Analog Camera stream splitted and shifted in y axis [BUG-142065]
- Widgets too slow [BUG-144337]
- Analog Camera channel switching slow [BUG-151151]
- CAN Symbol Pending flag has unexpected behavior [BUG-110992]
- Analog Video camera stream not smooth [BUG-142060]
- CAN Symbol stops to work after period of time [BUG-143953]
- SYS FAMILY not correct in recovery image [BUG-146786]
- API Specification signals table appears on the first page [BUG-148211]
- USB IP changed to default during system downgrade [BUG-146968]
- HWD contains only Preliminary datasheet [BUG-143271]
- Minimum GUIDE version is not correct [BUG-140877]
- Compile info seems to show HWD is still beta [BUG-140878]
- Analog Video is influencing alpha channel of fb1 [BUG-129256]

### 2.3 Known issues

- Video image is cropped and green line is visible [BUG-176754]
- DirAPI Copy big files in order performance issue [BUG-167897]
- Video of baudrate over 600kbps not playing smoothly [BUG-135858]
- WIFI STA random connection drops [BUG-129175]

## 3 Version DM1000 70312394v240 19.08r04 (Aug 2019)

### 3.1 What is New

- No new items.

### 3.2 Fixes to the HWD

- No fixes done.

### 3.3 Known issues

- DM1x00 Long Boot-up time [BUG-138314]
- M2M application download failed [BUG-138398]
- Video of baudrate over 600kbps not playing smoothly [BUG-135858]
- CAN23 baudrate change fails [BUG-135022]
- CAN not recover from BUS-OFF [BUG-129988]
- Analog Video is influencing alpha channel of fb1 [BUG-129256]
- WIFI STA random connection drops [BUG-129175]
- CAN Symbol Pending flag has unexpected behavior [BUG-110992]
- Revision History document - Section 2 is not updated [BUG-109977]
- HWD Revision History document is not generated [BUG-19364]

## 4 Product Information on the Web

For technical information, visit the Danfoss Power Solutions PLUS+1 website: ([PLUS1GuideSupport](#)).  
User Forum: (<http://www.plus1forum.danfoss.com>).

Telephone support can be obtained by calling:

North America: +1-763-509-2084

Europe: +46 476-569 06

Or call our toll-free number

North America: 1-888-50PLUS1 (+1-888-507-5871)

Please report all suggested enhancements and great ideas to ([plus+1helpdesk@danfoss.com](mailto:plus+1helpdesk@danfoss.com))

Please report all defects to ([plus+1helpdesk@danfoss.com](mailto:plus+1helpdesk@danfoss.com))

## 5 Disclaimer

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material.

Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed.

## 6 Copyright

©2004-2019 Danfoss A/S. All rights reserved.

All trademarks in this material are property of the respective companies.

Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.