

## Ordering no.: 176F4710

**FC 302 N160 T5 + FC 202 N200 T4 + FC 102 N200 T4**

**FC 302 N200 T5 + FC 202 N250 T4 + FC 102 N250 T4**

**FC 302 N250 T5 + FC 202 N315 T4 + FC 102 N315 T4**

Description	Code no.	Qty.
Control Card, FC 302 with safe stop	130B1109	1
Control Card, FC 102 with safe stop	130B1150	1
Control Card, FC 202 with safe stop	130B1167	1
Current Scaling	176F3156	1
Current Scaling	176F3157	1
Current Scaling	176F3158	1
Balance/HF Card	176F3161	1
Snubber Capacitor	176F3162	3
DC Bus Capacitor	176F3163	12
Heatsink Fan	176F3164	1
Mixing Fan	176F3165	1
IP20 Top Fan	176F3167	1
IP21/54 Door Fan	176F3169	1
Mains Fuse	176F3173	3
Mains Fuse	176F3174	3
IGBT Gate Drive Cable	176F3176	3
IGBT Temperature Cable	176F3178	1
Brake IGBT Gate Drive Cable	176F3180	1
Cable Inrush to SCR Gate D2h/D4h	176F3336	1
Rectifier SCR/Diode 503amp T4/T5 drive	176F3337	1
Door Fan Filter	176F3353	1
IGBT Module (600 amp)	176F3364	3
IGBT Module (900 amp)	176F3365	3
Brake IGBT Module (650 amp)	176F3367	1
Door Vent Kit	176F3375	1
Bus Bar Assembly	176F3386	1
Power Card Rugged NO 200kW 380-500V	176F3506	1
Power Card Rugged NO 250kW 380-500V	176F3507	1
Power Card Rugged NO 315kW 380-500V	176F3508	1
Power Card Rugged NO 200kW 380-480V	176F3512	1
Power Card Rugged NO 250kW 380-480V	176F3513	1
Power Card Rugged NO 315kW 380-480V	176F3514	1
Gate Drive Card	176F3515	1
Inrush Card	176F3517	1
SCR/Diode	176F8320	3
Mains Fuse	176F8335	3
Current Sensor	176F8342	3
Cable Control Card to Power Card D2h/D4h	176F3319	1
Current Sensor	176F8343	3
CONTAINER FOR SERVICE KIT	175Z2908	1
Current Sensor 300A	176F6515	3
Current Sensor 500A	176F6447	3
Control Card MKII with safe stop for FC-302/FC312	134B1726	1
Control Card MKII with safe stop for FC-102	134B1729	1
Control Card MKII with safe stop for FC-202	134B1731	1
DC Bus CAP 4700 uF 450 V	176F6634	12
Bus Bar Assembly CAP Bank 400V D1h/D3h	176F6765	1
Bus Bar Assembly CAP Bank 400V D2h/D4h	176F6767	1
Tool capacitor removal installation	176F6692	1