

Data sheet

Pressure transmitters for heavy duty applications

Types MBS 8200 and MBS 8250



MBS 8200 is a series of compact pressure transmitters developed to withstand the pressure pulsations and vibrations known in mobile and industrial hydraulic applications.

A new technology combining piezo resistive sensor element and programmable gain amplifiers makes the MBS 8200 the obvious choice for applications demanding highest accuracy and insensitiveness against temperature variations. Further this technology enhances the functional safety by limiting the output signal at excess pressure conditions, it allows excellent sink/source capabilities and it leave the pressure transmitters unaffected by electromagnetic fields up to 100 V/m.


MBS 8250 with integrated pulse-snubber is designed for use in tough applications with severe media influences like cavitation, liquid hammer or pressure peaks.

Features

- Designed for use in harsh industrial environments
- EMC protection 100 V/m up to 2 GHz;
20 V/m up to 4 GHz
- For media and ambient temperatures up to 125 °C
- 3.3 mA sink / source
- Reverse polarity protected
- Version with integrated pulse-snubber.
Protected against cavitation, liquid hammering and pressure peaks
- Enclosure and wetted parts of AISI 316L
- Digitally temperature calibrated
- Output clipping
- Fault indication / monitoring
- RoHS conformity

Approvals

UL 508
UL Hazloc; Class I, Div. 2, Group A – D

MBS 8250

Application

Cavitation, liquid hammer and pressure peaks may occur in hydraulic systems with changes in flow velocity, e.g. fast closing of a valve or pump starts and stops.

The problem may occur on the inlet and outlet side, even at rather low operating pressures.

The media viscosity has only little effect on the response time. Even at viscosities up to 100 cSt, the response time will not exceed 4 ms.

Technical data
Performance (EN 60770)

Accuracy @ 25 °C (incl. non-linearity, hysteresis and repeatability)	± 0.5% FS	
Non-linearity BFSL (conformity)	≤ ± 0.2% FS	
Hysteresis and repeatability	≤ ± 0.1% FS	
Total error band inside the compensated temperature range	≤ ± 1% FS	
Response time MBS 8200 (10-90%)	< 2 ms	
Response time MBS 8250 (10-90%)	Liquids with viscosity < 100 cSt	< 4 ms
	Air and gases	< 35 ms
Overload pressure (static)	Min. 6 × FS (max. 1400 bar)	
Burst pressure	> 6 × FS (max. 2000 bar)	
Durability, P: 10 – 90% FS	> 10 × 10 ⁶ cycles	

Electrical specifications

Nom. output signal (short-circuit protected)	4 – 20 mA (2-wire)	Ratiometric 10 – 90% of supply
Supply voltage [U _g], polarity protected	9 – 32 V d.c. > 32 V: Contact Danfoss	5 V d.c. ± 0.5 V
Supply – current consumption	–	≤ 6 mA
Supply voltage dependency	≤ ± 0.05% FS / 10 V	–
Current limitation	22 mA ± 0.5 mA	–
Sink / source	–	3.3 mA
Output impedance	–	≤ 25 Ω
Max load [R _L] (load connected to 0 V)	R _L ≤ (U _g - 9 V) / 0.02 A	R _L ≥ 1.5 kΩ

Technical data
(continued)

Environmental conditions


Media temperature range		-40 – 125 °C
Ambient temperature range		See page 6
Storage temperature		-50 – 125 °C
EMC - Emission		EN 61000-6-3
EMC Immunity	20 V/m, 80 MHz – 4 GHz	EN 61000-6-2
	100 V/m, 20 MHz – 2 GHz	ISO 11452-2
Surge protection		1 Kv @ 42 Ω; Line-Earth and Line-Line
Insulation resistance		> 100 MΩ at 500 V d.c.
Vibration stability	Sinusoidal	15.9 mm-pp, 5 Hz-25 Hz
		25 g, 25 Hz - 2 kHz
	Random	7.5 g _{rms} , 5 Hz – 1 kHz
Shock resistance	Shock	500 g / 1ms
	Free fall	1 m
Enclosure (depending on electrical connection)		See page 6

Mechanical characteristics

Materials	Wetted parts	EN 10088-1; 1.4404 (AISI 316 L)
	Enclosure	EN 10088-1; 1.4404 (AISI 316 L)
	Pressure connection	EN 10088-1; 1.4404 (AISI 316 L)
	Electrical connections	See page 6
Net weight (depending on pressure connection)		< 0.07 kg

Compensated temperature range: -20 – 100 °C.

Thermal shift outside the compensated temperature range: $\leq \pm 0.2\% FS / 10\text{ °K}$



Ordering

MBS 82..		-		-		-	
Type							Gasket
Standard	00						0 No gasket
With pulse snubber.	50						1 Gasket, Viton, media temp. -20 – 125 °C
Measuring range							Pressure connection
0 – 100 bar	30						GB 04 G ¼, DIN 3852-E / ISO 1179-2
0 – 160 bar	32						AC 04 ¼ –18 NPT, ANSI/ASME B 1.20.1, excl. gasket
0 – 250 bar	34						BD 08 7/16 – 20 UNF-2A, ISO 11926-2
0 – 400 bar	36						FA 08 M14 x 1.5, ISO 6149-2
0 – 600 bar	38						
0 – 1500 psi	72						Electrical connection (connections see page 4)
0 – 3000 psi	76						A 2 AMP Econoseal, J series, 3-pin, male, excl. female plug
0 – 5000 psi	78						B 2 AMP Junior Power Timer, 2-pin, male, excl. female plug
0 – 6000 psi	79						C 2 Round Packard Metri-Pack, 3-pin, male, excl. female plug
0 – 7500 psi	80						A 8 AMP Super seal, 3-pin, male, excl. female plug,
0 – 9000 psi	81						on 125 mm. Flying leads
Compensated temperature range							
-20 – 100 °C						33	
Pressure reference							
Gauge (relative)							1
Absolute							2
Output signal							
4 – 20 mA							1
Ratiometric, 10 – 90%							6





Please contact your local Danfoss office for further information or request on other versions.

Dimensions/Combinations

Type code	A2	B2	C2	A8
Electrical connection	AMP Econoseal	AMP Junior Power Timer	Round Packard Metri-Pack	Flying leads with AMP superseal
Housing: ø = 19 mm				
Pressure connection				
	G $\frac{1}{4}$ – DIN 3852-E Gasket: DIN 3869-14	$\frac{1}{4}$ – 18 NPT	$\frac{7}{16}$ – 20 UNF-2A O-ring	M14 x 1,5 – ISO 6149-2 O-ring
22 mm				
Type code	GB04	AC04	BD08	FA08
Recommended torque ²⁾	30 – 35 Nm	2 – 3 turns after finger teightend	30 – 35 Nm	30 – 35 Nm

²⁾ Depends of different parameters as packing material, mating material, thread lubrication and pressure level.

Electrical connections

Type code		A2	B2	C2	A8
					
		AMP Econoseal, J series male	AMP Junior power timermale	Round Packard Metri-Pack, male	Flying leads, 125 mm with AMP superseal 1.5 series, male
Ambient temperature	4 – 20 mA	-30 – 105 °C	-30 – 105 °C	-40 – 105 °C	-40 – 105 °C
	Ratiometric	-30 – 105 °C	–	-40 – 125 °C	-40 – 125 °C
Enclosure (IP protection fulfilled together with mating connector)		IP67	IP67	IP67	IP67
Materials		Glass filled polyamide, PA 6.6 Sn-coated contacts	Glass filled polyamide, PA 6.6 Sn-coated contacts	Glass filled polyamide, PA 6.6 Sn-coated contacts	Glass filled polyamide, PA 6.6 Wire: PETFE (teflon) Protection sleeve: Polyester braided. Sn-coated contacts
Electrical connection	4 – 20 mA (2 wire)	Pin1: + supply Pin 2: ÷ supply Pin 3: not used	Pin 1: + supply Pin 2: ÷ supply	Pin1 (A): ÷ supply Pin 2(B): + supply Pin 3(C): not used	Pin 1: + supply Pin 2: ÷ supply Pin 3: not used
	Ratiometric	Pin 1: + supply Pin 2: ÷ supply Pin 3: output	–	Pin 1 (A): ÷ supply Pin 2(B): + supply Pin 3(C): output	Pin 1: + supply Pin 2: ÷ supply Pin 3: output

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.