

Remote access of cold rooms with Optyma™ Control keeps you in control

Optyma $^{\text{\tiny{M}}}$ Control with RS485 ADAP-KOOL $^{\text{\tiny{0}}}$ compatible Modbus offers remote and accurate control of cold rooms .

Optyma[™] Control provides HACCP temperature monitoring in compliance with EN13485 Class II. Thanks to the unique built-in differential magnetothermic circuit breaker, which guarantees safety by cutting the general power supply, Optyma[™] Control offers both control and protection in a single unit.

Optyma™ Control with RS485

as stand-alone or integrated in a complete ADAP-KOOL® system.





Optyma™ Control, single-phase

Power supply

Voltage	230 V AC ± 10% 50/60 Hz
Max absorbed power	~7VA
(electronic control)	

Ambient conditions

Operating temperature	-5 to +50°C
Storage temperature	-30 to +70°C
Relative humidity	< 90% RH

General characteristics

Connectable sensor types	NTC 10K 1%
Resolution	0.1 ℃
Probe tolerance	± 0.5 ℃
Operating range	-45+45 °C

Output characteristics - max. applicable load (230 V AC)

Compressor	1500 W (AC3)
Defrost	3000 W (AC1)
Fans	500 W (AC3)
Room light	800 W (AC1)
Configurable alarm contact / aux (voltage-free contact)	100 W

General electric protection

Bipolar differential magnetothermic	16A ld = 300 mA switching power 4.5 kA
circuit breaker	Id = 30 mA (on request)

Insulation and mechanical characteristics

Cover protection rating	IP 65	
Cover material	self-extinguishing ABS	
Type of insulation	Class II	
Box dimensions	262 x 168 x 97	

Ordering

Туре	Code no.
Optyma™ Control, single-phase (2 HP)	080Z3200

Applications:

- Complete control of single-phase static or ventilated refrigeration systems up to 2 HP, with off-cycle or electrical defrosting and direct or pump-down compressor stop.
- Evaporator control via liquid line solenoid valve.

Main characteristics:

- Guaranteed certified safety and protection thanks to incorporated differential magnetothermic circuit breaker, which cuts the general power supply.
- Simple wiring and live outputs.
- · New hinged cover for ease of installation and opening.
- Transparent cover for access to magnetothermic breaker, all with IP 65 protection rating.
- Simple, flexible programming for optimum versatility.

- HACCP temperature monitoring in compliance with EN13485 Class II.
- · Remote control with RS485 Modbus.
- Compressor can be run in pump-down stop mode.
- Integration of control and protection in a single roomdedicated unit reduces installation time and costs.

Options:

· Hot-gas defrost control.

Optyma™ Control, three-phase

	Optyma™ Control, three-phase (4 HP)	Optyma™ Control, three-phase (7.5 HP)
Case dimensions	400 x 300 x 135 mm	400 x 300 x 135 mm
Protection rating	IP 65	IP 65
Power supply (3F + N + T)	400 V AC ±10% 50/60Hz	400 V AC ±10% 50/60Hz
Load type	three-phase	three-phase
Operating temperature	-5 to +40°C	-5 to +40°C
Storage temperature	-25 to +55°C	-25 to +55°C
Relative ambient humidity	< 90% RH	< 90% RH
Main switch / general protection	4 poles magnetothermic 16A	4 poles magnetothermic 25A
Compressor protection	motor circuit breaker	motor circuit breaker
Defrosting	electrical	electrical
Status indicators	LED + display	LED + display
Alarm signals	LED + buzzer	LED + buzzer

Inputs

Ambient probe	NTC 10K 1%	NTC 10K 1%
Evaporator probe	NTC 10K 1%	NTC 10K 1%
Door switch	present	present
High/low pressure switch	present	present
Kriwan® connection	present	present
Compressor functioning mode selection	pump-down / thermostat	pump-down / thermostat

Outputs

Outputs		
Compressor	370 W to 3000 W (0.5 to 4 HP)	3000 W to 5500 W (4 to 7.5 HP)
Condenser fans output 1	800 W (1ph)	800 W (1ph)
Condenser fans output 2 (separated)		total (1ph)
Evaporator fans	500 W (1ph)	2000 W (1ph / 3ph)
Defrosting heaters	6000 W	9000 W
Room light	800 W (AC1) resistive load	800 W (AC1) resistive load
Solenoid valve	present	present
Compressor oil heater	present	present
Alarm relay	100 W	100 W

Ordering

Туре	Code no.
Optyma [™] Control, three-phase (4 HP) 4.5-6.3 A	080Z3201
Optyma [™] Control, three-phase (4 HP) 7-10 A	080Z3202
Optyma [™] Control, three-phase (7.5 HP) 11-16 A	080Z3206
Optyma [™] Control, three-phase (7.5 HP) 14-20 A	080Z3207

Applications:

 Control of three-phase refrigeration plant up to 7.5 HP, static or ventilated, with off-cycle or electrical defrosting.

Main characteristics:

- Direct control of the compressor, condenser fans, compressor oil heater, defrosting heaters, evaporator fans, solenoid valve, room light and all standardcompliant electrical safeguards.
- Differential magnetothermic circuit breaker (for cutting the general power supply) accessible from the front panel.
- Adjustable motor circuit breaker for compressor protection accessible from the front panel.
- Easy wiring on the internal terminal block.
- Selection of functioning mode for the compressor (pumpdown / thermostat).

- HACCP temperature monitoring in compliance with EN13485 Class II.
- Remote control with RS485 Modbus.
- Auxiliary relay with activation configurable by parameter.
- Transparent cover for access to magnetothermic circuit breaker, all with IP 65 protection rating.
- Electronic control with wide LED display and easy-to-use buttons.
- Status signaling with LED icons.



Dimensions




Optyma™ Control, single-phase





Optyma™ Control, three-phase

Connection diagrams



Optyma™ Control, single-phase





Optyma™ Control, three-phase (7.5 HP)

Complete portfolio from Danfoss for control of your refrigeration plant



ADAP-KOOL™ systems



Optyma[™] condensing units







Remote control of cold rooms and convenience stores

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed.

All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarkes of Danfoss A/S. All rights reserved.

©Danfoss | DSC (hp) | 2016.02