

# TTY6F

## High Energy-optimized Compressor

### R134a

### 115V 60Hz

Data Sheet (Replaces CG.42.R1.22)

#### General

Compressor		TTY6F
Connector-material	Sealing	Code number
Copper-plated steel	Aluminium caps	
Copper-plated steel	Rubber plugs	102G3647
Copper	Rubber plugs	

#### Application

Application		LBP
Evaporating temperature range	°F (°C)	-31 to 14 (-35 to -10)
Voltage range	V/Hz	103 - 127 /60
Motor type		RSCR*
Max. ambient temperature	°F (°C)	110 (43)
Comp. cooling at max. ambient temperature	110°F (43°C)	S

\*run capacitor compulsory

#### Design


Displacement	cu.in. (cm <sup>3</sup> )	0.35 (5.70)
Oil quantity	fl.oz. (cm <sup>3</sup> )	6.1 (180)
Maximum refrigerant charge	oz. (g)	14.0 (400)
Free gas vol. in compressor housing	fl.oz. (cm <sup>3</sup> )	60.7 (1790)
Weight without electrical equipment	lbs. (kg)	17.6 (8.0)

#### Motor


Motor size	watt	200
LRA (rated after 4 sec. UL984) LST	A	14.4
Cut-in current LST	A	25.2
Resistance, main and start winding (77°F)	Ω	2.8/3.2
Approvals		UL984/CSA-C22.2

#### Dimensions

Height	in. (mm)	A	6.81 (173)
		B	6.65 (169)
Suction connector	location/I.D. in. (mm)	C	0.252-0.259 (6.5±0.09)
Process connector	location/I.D. in. (mm)	D	0.252-0.259 (6.5±0.09)
Discharge connector	location/I.D. in. (mm)	E	0.202-0.205 (5.0+0.12/0.20)
Compressors on a pallet	pcs.		125



- S = Static cooling normally sufficient
- O = Oil cooling
- F<sub>1</sub> = Fan cooling 1.5 m/s (compressor compartment temp. equal to ambient temperature)
- F<sub>2</sub> = Fan cooling 3.0 m/s necessary



**Capacity (ASHRAE)**
**Btu/h**

Comp.°F	-30	-20	-13	-10	0	10	14
Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
TTY6F	294	437	555	611	825	1084	1202

**Capacity (EN 12900/CECOMAF)**
**watt**

Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
Comp.°F	-30	-20	-13	-10	0	10	14
TTY6F	70	105	133	146	197	259	287

**Power consumption**
**watt**

Comp.°F	-30	-20	-13	-10	0	10	14
Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
TTY6F	91	112	127	133	154	178	189

**Current consumption**
**A**

Comp.°F	-30	-20	-13	-10	0	10	14
Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
TTY6F	1.05	1.18	1.29	1.34	1.52	1.73	1.81

**EER (ASHRAE)**
**Btu/Wh**

Comp.°F	-30	-20	-13	-10	0	10	14
Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
TTY6F	3.21	3.88	4.39	4.61	5.36	6.09	6.36

**COP (EN 12900/CECOMAF)**
**W/W**

Comp.°C	-34.4	-28.9	-25	-23.3	-17.8	-12.2	-10
Comp.°F	-30	-20	-13	-10	0	10	14
TTY6F	0.77	0.93	1.05	1.10	1.28	1.46	1.52

Test conditions	ASHRAE	EN 12900/CECOMAF
Condensing temperature	130°F (54,4°C)	55°C (131°F)
Ambient and suction gas temp.	90°F (32°C)	32°C (90°F)
Liquid temperature	90°F (32°C)	55°C (131°F)
Static cooling, with RC 15 µF, 115V 60Hz, PTC consumption incl.		

**Accessories**

Devices	Fig.	TTY6F
PTC starting device (Texas Instr.) with reduced loss of energy	a1	117U6102
		TI 8EA 4B3
PTC starting device (Siemens) with reduced loss of energy	a1 (alternative)	117U6106
		J506-A120-A320
Cover	b	117U1026
Run capacitor 15 µF (compulsory)	e	117-7118
Protector (Texas Instruments)	f	117U3303
		TI-4TM414KFBYY-53
Mounting accessories	Ø in. (mm)	
Bolt joint for one compressor	5/8 (16)	118-1946
Bolt joint for one compressor	3/4 (19)	118-1949
Snap-on for one compressor	5/8 (16)	118-1947

