



TYPE APPROVAL CERTIFICATE
No. ELE006715XG/002

This is to certify that the product below is found to be in compliance with the applicable requirement of the RINA type approval system.

<i>Description</i>	Temperature transmitters
<i>Type</i>	Series MBT 5560
<i>Applicant</i>	DANFOSS A/S Nordborgvej 81 DK-6430 Nordborg (office E14-S1) DENMARK
<i>Manufacturer</i>	DANFOSS (TIANJIN) LTD. - INDUSTRIAL AUTOMATION
<i>Place of manufacture</i>	BUSINESS UNIT WUQUING DEVELOPMENT AREA, 9 QUANHUI ROAD 31700 TIANJIN CHINA
<i>Reference standards</i>	Rules for the Classification of Ships - Part C - Machinery, Systems and fire protection - Ch.3, Sect.6, Tab.1.

Issued in **HAMBURG** on **January 12, 2015**. This Certificate is valid until **January 11, 2020**


RINA Services S.p.A.
Giuseppe Russo

This certificate consists of this page and 1 enclosure



TYPE APPROVAL CERTIFICATE

No. ELE006715XG/002

Enclosure - Page 1 of 1

Series MBT 5560

MBT 5560 temperature sensor with integrated transmitter, designed for use in harsh maritime environments

Description:

Measuring range	-50 to 200°C
Power supply voltage	10 to 32Vcc (4-20mA) and 4.75 to 8Vdc (Ratiometric)
Output signal	4-20 mA or Ratiometric
Accuracy	±0.5% F.S. (typ.)
Protection tube	AISI 316 TI
Extension length	0 or 33 mm
Insertion length	50 to 250 mm
Transmitter setting	- 50°C to 200°C, min. Span 25°C
Process connection	G 1/4 A or larger , M14 or larger, NPT 1/4 - 18 or larger
Electrical connection	plug EN 175301/803, PG9 plug AMP Econoseal, J series, male plug IEC 947-5-2, M12x1, male screened cable 2m

Reference document:

Danfoss data sheet: doc. n° IC.PD.P30.F6.02 / 520B6279 dated 2014-05.

Test Reports:

Mechanical , Climatic, EMC according to IACS UR E10 in force.

This certificate annuls and replaces the previous one n° ELE030010CS/009.

HAMBURG January 12, 2015



A handwritten signature in blue ink, appearing to read 'Syr Dan', located to the right of the redacted area.