



Solid core liquid line filter drier 03 cu in.													
Refrigeration and Air Conditioning													
Type	Connection	Liquid capacity [kW] / [TR]						Drying capacity [kg] / [lbs], t = 24 °C					
		R 134A	R 404A	R 507	R 22	R 407C	R 410A	R 134A	R 404A	R 507	R 22	R 407C	R 410A
DML/DCL 032	1/4 in. flare	6.77 (1.90)	5.01 (1.42)	4.86 (1.38)	7.45 (2.12)	7.09 (2.02)	7.43 (2.11)						
DML/DCL 032S	6 mm or 1/4 in. ODF												
DML/DCL 032.5S	8 mm or 5/16 in. ODF	9.59 / (2.73)	6.97 / (1.98)	6.75 / (1.92)	10.52 / (2.99)	9.97 / (2.84)	10.31 / (2.93)						
DML/DCL 033	3/8 in. flare	12.85 / (3.65)	9.86 / (2.80)	9.57 / (2.72)	14.46 / (4.11)	13.84 / (3.94)	14.67 / (4.17)	5.0 / (11.02)	5.3 / (11.68)	5.4 / (11.90)	5.0 / (11.02)	5.0 / (11.02)	4.5 / (9.92)
DML/DCL 033S	10 mm or 3/8 in. ODF							DCL	DCL	DCL	DCL	DCL	DCL
DML/DCL 034	1/2 in. flare							3.9 / (8.59)	4.2 / (9.25)	4.2 / (9.25)	3.9 / (8.59)	3.9 / (8.59)	3.5 / (7.71)
DML/DCL 034S	12 mm or 1/2 in. ODF	24.71 / (7.03)	20.12 / (5.72)	19.57 / (5.56)	28.60 / (8.13)	27.65 / (7.86)	30.13 / (8.57)						

ELIMINATOR®

The Danfoss ELIMINATOR® Series of filter driers are the most effective all-purpose driers available today. Choose the core composition that's right for your system:

DML - 100% molecular sieve.
Designed for applications requiring
the highest moisture capacity.

DCL - 80% molecular sieve
with 20% activated alumina.
Designed for applications requiring
high moisture capacity and acid
adsorption capacity.