



ELIMINATOR®
Liquid line filter drier

Solid core liquid line filter drier 08 cu in.													
Refrigeration and Air Conditioning													
Type	Connection	Liquid capacity [kW] / [TR]						Drying capacity [kg] / [lbs], t = 24 °C					
		R 134A	R 404A	R 507	R 22	R 407C	R 410A	R 134A	R 404A	R 507	R 22	R 407C	R 410A
DML/DCL 082	1/4 in. flare	7.68 / (2.18)	5.44 / (1.55)	5.27 / (1.50)	8.32 / (2.37)	7.85 / (2.23)	8.02 / (2.28)	DML: 12.6 / (27.9)	DML: 13.6 / (29.9)	DML: 13.8 / (30.5)	DML: 12.8 / (28.2)	DML: 12.7 / (27.9)	DML: 11.5 / (25.4)
DML/DCL 082S	6 mm or 1/4 in. ODF												
DML/DCL 082.5S	8 mm or 5/16 in. ODF	10.53 / (3.00)	7.84 / (2.23)	7.61 / (2.16)	11.69 / (3.32)	11.13 / (3.16)	11.63 / (3.31)						
DML/DCL 083	3/8 in. flare	14.19 / (4.03)	10.98 / (3.12)	10.66 / (3.03)	16.03 / (4.56)	15.37 / (4.37)	16.35 / (4.65)						
DML/DCL 083S	10 mm or 3/8 in. ODF												
DML/DCL 084	1/2 in. flare	28.61 / (8.14)	21.33 / (6.07)	20.68 / (5.88)	31.76 / (9.03)	30.24 / (8.60)	31.63 / (8.99)	DCL: 9.8 / (21.7)	DCL: 10.6 / (23.3)	DCL: 10.8 / (23.80)	DCL: 10.0 / (22.0)	DCL: 9.9 / (21.8)	DCL: 9.0 / (19.8)
DML/DCL 084S	12 mm or 1/2 in. ODF												
DML/DCL 085	5/8 in. flare	43.81 / (12.46)	35.32 / (10.04)	34.33 / (9.76)	50.47 / (14.35)	48.71 / (13.85)	52.83 / (15.02)						
DML/DCL 085S	16 mm or 5/8 in. ODF												

ELIMINATOR®

The Danfoss ELIMINATOR® Series of filter driers are the most effective all-purpose driers available today. Choose the core composition that's right for your system:

DML - 100% molecular sieve. Designed for applications requiring the highest moisture capacity.

DCL - 80% molecular sieve with 20% activated alumina. Designed for applications requiring high moisture capacity and acid adsorption capacity.

993B9856