



TYPE APPROVAL CERTIFICATE

Certificate No. : HMB28683-AC001 **Initial Approval :** 28th July, 2014
Product : Frequency Converter
Manufacturer : Vacon Ltd.
Runsorintie 7, 65380 Vaasa, Finland

Product Description : Variable speed drives for asynchronous motors
– Type : NXP, NXA, NXN, NXI, NXS series
" See Appendix 1 "

Approval Condition : " See Appendix 1 "

THIS IS TO CERTIFY that the above-mentioned product has been approved in accordance with the relevant requirement of this Society's Rules and / or of the recognized standards as follows and entered in the "List of Approved Manufacturers and Type Approved Equipment".

Pt. 6, Ch. 2, Art. 301 of the Rules for Classification, Steel Ships.

This Certificate is valid until 27th July, 2024

Issued at Busan, Korea on 21st August, 2019



This certificate is signed electronically in accordance with IMO FAL.5/Circ.39/Rev.2. Validation and authentication of the certificate can be confirmed from "<http://e-cert.krs.co.kr>" by using the tracking No (ME19022228464) and certificate No.(HMB28683-AC001).



KOREAN REGISTER OF SHIPPING

General Manager of
Marine & Ocean Equipment Team

- Note :** 1. This certificate will be valid subject to complying with the approval conditions described on the certificate and/or on the Rules of this Society.
2. This certificate will be invalid from the expiry date aforementioned unless the extension or renewal has been granted to the applicant or the manufacturer.
3. Any significant modifications or changes in design or construction to the above product without approval from this Society will render this certificate invalid.
4. Should the specified rules, regulations or standards be amended during the validity of this certificate, the product is to be re-approved by this Society in accordance with the requirements as amended.

Appendix 1

Product Description and/or Approval Condition

Certificate No : HMB28683-AC001

Date of Issue : 21st August, 2019

A. Product Description

1. Product Specification

1) NXS industrial drive

- Rated voltage & motor power
 - 208 ~ 240 V, 3 phase : 0.37 ~ 75 kW
 - 380 ~ 500 V, 3 phase : 0.75 ~ 400 kW
 - 525 ~ 690 V, 3 phase : 2.2 ~ 560 kW
- Frame (Air cooled) : FR4 ~ FR12
- Degree of protection : IP 00, IP 21 & IP 54

2) NXP High Performance Drive

- Rated voltage & motor power
 - 208 ~ 240 V, 3 phase : 0.30 ~ 75 kW
 - 380 ~ 500 V, 3 phase : 0.75 ~ 1500 kW
 - 525 ~ 690 V, 3 phase : 2.2 ~ 2000 kW
- Frame (Air cooled) : FR4 ~ FR14, FI9 ~ FI13
- Degree of protection : IP 00, IP 21 & IP 54

3) NXP Liquid Cooled Drive

- Rated voltage & motor power
 - 380 ~ 500 V, 3 phase : 7.5 ~ 5150 kW
 - 525 ~ 690 V, 3 phase : 5.5 ~ 5300 kW
- Frame (Liquied cooled) : CH3, CH4, CH5, CH61, CH62, CH63, CH64, CH72, CH74
- Degree of protection : IP 00

* Remark

- a) NXP can be substituted by NXA, NXN & NXI by application selection.
- b) All drive can be accompanied with external components as follows.
 - brake chopper, brake resistors, AC chokes, filters(SIN-, RFI-, DUT-, LCL)

2. Documentation

1) Test reports

- EMC test reports no. 228338-1, 231330-1, 234713-1 issued by SGS
- Environmental test reports no. VTT-S-00992-09 issued by VTT
- FR6 & FR8 Damp heat test report issued by VACON
- FR6 Vibration test report issued by Centria
- Other test data for CH3 ~ CH7, FR4 ~ FR14
- SGS Fimko test report No. 282088-1 (IEC 61800-5-1)
- Vacon Doc. "CH60 Liquid Cooled NFE 400-690V Summary of IEC 61800-5-1 Type tests" rev.V001 dated 2016-01-19

2) Circuit diagrams & outline drawings for CH3 ~ CH7, FR4 ~ FR14

3) User Manual

- Vacon NX Inverters FI4~8 User Manual
- Vacon NX Inverters FI9~14 User Manual
- Vacon NXP IP00 Modules FR10~14 Installation Manual
- Vacon NXP Liquid Cooled Drives User Manual
- Vacon NXS NXP User Manual

4) Brochure, Product Statements & Quality Certificates

B. Approval Condition

1. This approval is granted on the basis of the test reports & submitted documents.
2. The product or packing is to be marked with manufacturer name and type designation on a suitable position.
3. The actual installation is to be designed to Manufacturer's manual & KR Rule Pt. 6, Ch. 1 & 2.
4. If the converters are used as parts of the motor controller which drive essential auxiliaries specified in KR Rule Pt. 5, Ch. 1, 102 and exceed the output 7.5 kW, Individual Product Certification is required for the motor controller.

< End of Certificate >