




ITEM	PART NUMBER	QTY	COMMENTS
1	132a1214-01 70cmc12662-01	1	
2	132a1214-02 70cmc12662-02	1	
3	TPS-3MM-8	2	

POLYURETHANE FOAM
FERMAPOR K31-A-9316-3 + K31-B-81



SECTION A-A
2.0 THK.

- NOTES:
1. BEND RELIEFS TO BE EQUAL TO THE MATERIAL THICKNESS, UNLESS NOTED.
 2. BURR ALLOWABLE TO 15 PERCENT OF MATERIAL THICKNESS.
 3. INSIDE BEND RADII TO BE EQUAL TO THE MATERIAL THICKNESS, UNLESS NOTED.

- ⊕ CRITICAL CHARACTERISTICS
 - ▽ KEY CHARACTERISTICS
 - INSPECTION
- MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

UNLESS OTHERWISE SPECIFIED INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS .X±0.4 .XX±0.20 < ±1.0		THIRD ANGLE PROJECTION	SCALE 0.250	SIZE A3	MATERIAL DX51D+Z275MAC GALV. STEEL / EN10327; S=2.0
— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP				DESCRIPTION FAB, BRKT, DX51D, GLAND PLATE IP54 UL, 1XAAF	
CHANGED				DRAWING NUMBER 132a1214 (70cmc12662)	REV 001
DESIGNED	KANNAN 05/24/17			MODEL 132a1214 (70cmc12662)	SHEET 1 OF 1
CHECKED		CONFIDENTIAL: PROPERTY OF DANFOSS A/S NØRDBØRG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			