

MAINS

MOTOR


◻ CRITICAL CHARACTERISTICS  
 ▽ KEY CHARACTERISTICS  
 ○ INSPECTION  
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED .3±1.0 .X±0.50 <math>\angle\pm 1.0</math>			THIRD ANGLE PROJECTION 	SCALE 0.188	SIZE A1	MATERIAL  FINISH  DESCRIPTION
PMW CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP						
CHANGED BC 05/11/18	DESIGNED ML 10/15/08	CHECKED   			DWG. REF. TERMINAL, SIDE ENTRY	
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.						

MOTOR													
FRAME	CAB. (MM)	A	B	C	D	E	F	G	H	I	J	K	L
F1-F4	400	157.0 [6.18]	209.0 [8.23]	NA	NA	NA	NA	140.2 [5.52]	192.2 [7.57]	244.2 [9.61]	NA	NA	NA
	600	152.0 [5.98]	204.0 [8.03]	256.0 [10.08]	308.0 [12.13]	360.0 [14.17]	412.0 [16.22]	165.2 [6.50]	217.2 [8.55]	269.2 [10.60]	321.2 [12.65]	373.2 [14.69]	425.2 [16.74]

MAINS																		
FRAME	CAB. (MM)	AA	BB	CC	DD	EE	FF	GG	HH	II	JJ	KK	LL	MM	NN	OO	PP	QQ
F1/F2	400	153.5 [6.04]	205.5 [8.09]	NA	NA	NA	NA	145.1 [5.71]	205.1 [8.08]	265.1 [10.44]	1130.7 [44.52]	930.7 [36.64]	730.7 [28.77]	118.9 [4.68]	002	002	002	301.6 [11.87]
	600	150.5 [5.93]	202.5 [7.97]	254.5 [10.02]	306.5 [12.07]	358.5 [14.11]	410.5 [16.16]								149.0 [5.86]	196.6 [7.74]	244.2 [9.61]	
F3/F4	400	153.5 [6.04]	205.5 [8.09]	NA	NA	NA	NA	115.9 [4.56]	175.9 [6.92]	235.9 [9.29]	1230.0 [48.43]	1030.0 [40.55]	830.0 [32.68]	195.7 [7.70]	002	002	002	355.2 [13.98]
	600	150.5 [5.93]	202.5 [7.97]	254.5 [10.02]	306.5 [12.07]	358.5 [14.11]	410.5 [16.16]								129.8 [5.11]	177.4 [6.98]	225.0 [8.86]	

400MM CABINET



600MM CABINET

