

ENGINEERING  
TOMORROW

*Danfoss*

Danfoss ELIMINATOR® 1.5 in<sup>3</sup> filter drier

Keep the **smallest** refrigeration applications **dry, clean** and **safe**

Designed for Glass Door Merchandisers and other light commercial applications.

Works with  
pressures up to

**46 bar**  
(667 psig)



# Single



## Available filter drier options

Code	Type	Inlet Port	Connector Size		Qty per box	Packing Format
			Inlet	Outlet		
023Z8252	DCL 1.52s XL / 2.8mm s	Single	1/4 XL	2.8 mm	36	I-Pack
023Z8253	DML 1.52s	Single	1/4	1/4	36	I-Pack
023Z8254	DML 1.52s	Single	1/4	1/4	32	M-Pack
023Z8255	DCL 1.52 / 2.8mm s	Single	1/4	2.8 mm	32	M-Pack
023Z8258	DML 1.52s XL	Single	1/4 XL	1/4 XL	36	I-Pack
023Z8260	DCL 1.52s	Single	1/4	1/4	36	I-Pack

# Dual



## Available filter drier options

Code	Type	Inlet Port	Connector Size		Qty per box	Packing Format
			Inlet	Outlet		
023Z8250	DML 1.52x2/2s	Dual	1/4	1/4	36	I-Pack
023Z8256	DML 1.52-2.5 / 2s	Dual	1/4 - 5/16	1/4	36	I-Pack
023Z8257	DML 1.52x2 / 2.8mm s	Dual	1/4	2.8 mm	36	M-Pack
023Z8259	DML 1.52x2 / 2.3mm s	Dual	1/4	2.3 mm	36	M-Pack
023Z8262	DML 1.515-2x2 / 2.5mm s	Dual	3/16	2.5 mm	36	I-Pack

# Robust, compact and reliable

Filter driers keep refrigeration systems dry and clean to protect against corrosion and other contamination that may impede system performance or result in breakdown of the refrigeration unit. An effective filter drier also ensures that oil and refrigerant do not decompose thus extending system performance and life.


Danfoss ELIMINATOR® 1.5 in<sup>3</sup> filter drier has been optimized for glass door merchandisers and other light commercial applications. It is specially designed to minimize the amount of refrigeration system charge and assists designers in meeting the strict 150g system limits when using flammable refrigerants such as R290 (propane). The ELIMINATOR® filter drier has a solid core that yields a fast adsorption rate and no loose dessicant which can add unwanted particles to the refrigerant. It is also designed for superior flow capacity as well as low pressure drop and these combined benefits minimize operation and maintenance costs.

## Available connectors

Different solder connectors regarding diameter and total length available for combination.


### Single

#### 1/4" ODF Std




### Dual


#### 1/4" ODF Std




#### 1/4" ODM XL



#### 2.8 mm ODF XL




#### 1/4" ODF XL




# Technical Data

Type	DML 1.52x2/2s	DCL 1.52XL/2.8mm s
Weight	0.12 Kg / 0.26 lbs	0.12 Kg / 0.26 lbs
Refrigerant	HCFC; HFC; HC; HFO	
Paint	Powder coating gloss 90, RAL 9005 (Black)	
Max. Working Pressure/PB	46 bar / 667 psig (fatigue test)	
Solid Core:		
Volume	24 cm <sup>3</sup> / 1.49 in <sup>3</sup>	
Surface Area	46 cm <sup>2</sup> / 7.20 in <sup>2</sup>	
Net Volume	0.036 l / 1.21 f oz US	
Shell Volume	0.050 l / 1.70 f oz US	
Media Temperature	-40 °C → +70 °C / -40 °F → 160 °F	
Core Composition	100% Molecular Sieve	80% Molecular Sieve 20% Activated alumina
Water adsorption capacity (kg of ref. / drops H <sub>2</sub> O):		
R134a	t <sub>i</sub> =24°C: 2.9 kg / 58 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.7 kg / 55 H <sub>2</sub> O	t <sub>i</sub> =24°C: 2.3 kg / 45 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.1 kg / 43 H <sub>2</sub> O
R404A	t <sub>i</sub> =24°C: 3.1 kg / 61 H <sub>2</sub> O t <sub>i</sub> =52°C: 3.0 kg / 57 H <sub>2</sub> O	t <sub>i</sub> =24°C: 2.4 kg / 47 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.3 kg / 45 H <sub>2</sub> O
R32	t <sub>i</sub> =24°C: 2.7 kg / 51 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.5 kg / 46 H <sub>2</sub> O	t <sub>i</sub> =24°C: 2.1 kg / 40 H <sub>2</sub> O t <sub>i</sub> =52°C: 1.9 kg / 36 H <sub>2</sub> O
R290	t <sub>i</sub> =24°C: 3.5 kg / 54 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.8 kg / 44 H <sub>2</sub> O	t <sub>i</sub> =24°C: 2.8 kg / 42 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.2 kg / 34 H <sub>2</sub> O
R600a	t <sub>i</sub> =24°C: 3.2 kg / 61 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.6 kg / 49 H <sub>2</sub> O	t <sub>i</sub> =24°C: 2.5 kg / 48 H <sub>2</sub> O t <sub>i</sub> =52°C: 2.0 kg / 38 H <sub>2</sub> O
Flow capacity at Δp = 0.07 bar / 1psi:		
R134a	1.7 Ton / 5.97 kW	1.7 Ton / 5.97 kW
R404A	1.2 Ton / 4.21 kW	0.8 Ton / 2.81 kW
R32	2.5 Ton / 8.78 kW	1.2 Ton / 4.21 kW
R290	2.0 Ton / 7.02 kW	1.0 Ton / 3.51 kW
R600a	2.1 Ton / 7.37 kW	1.0 Ton / 3.51 kW

## Single



## Dual



# Refrigeration and Air Conditioning Danfoss Product Lines

Danfoss, global leader in refrigeration and air conditioning technologies, provides intelligent solutions to the growing global need for infrastructure, food, and energy and climate industry. In Latin America, Danfoss specializes in the production of components for commercial, industrial refrigeration, air conditioning and energy.

Since 1933, Danfoss keeps innovating continuously, engineering for a future in which the companies are more efficient, reduce costs and care for the environment. Present in Apodaca Nuevo León, Mexico since 1995, with administrative offices and manufacturing plant.



*Commercial  
Refrigeration Controls*



*Industrial Refrigeration  
Controls*



*Sensors and Electronic  
Controls*



*Industrial Automation  
Controls*



*Fractional Compressors*



*Commercial  
Compressors*



*Condensing Units*



*Thermostats*

## Contact Us

**Customer Service** | 01800 823 80 00

**Sales-Mexico** | [mexico@danfoss.com](mailto:mexico@danfoss.com)

**Sales- Central America and Caribbean Sales** | [cac@danfoss.com](mailto:cac@danfoss.com)

**Technical Support** | [soporte.tecnico@danfoss.com](mailto:soporte.tecnico@danfoss.com)

Danfoss Industries, S.A. de C.V. | Miguel Alemán 162, El Milagro 66634 | Apodaca, N.L. México

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.