






additional informations:
 filter colour : impregnated
 filter weight : 36kg



Detail A:
 scale 2:1

label:

ULT MCC 102 du/dt FILTER
 www.danfoss.com

Part no. 0908115
 PIN: 130B2849
 3x 380-690V, 50/60Hz (max: 100Hz)
 3x 480-690V, 41.5kVA @ 500V 344A @ 690V 200A @ 690V
 Chassis/PCB Temp. $45^{\circ}\text{C}/75^{\circ}\text{C}$
 130B2849/00169-2016

Use only with a type 1 or type 2 SPD overvoltage control device

UL LISTED E37002 E 0908115
 UL Classified
 UL Impregnated

MADE IN GERMANY
 L=30H
 C=43H
 F=58H
 W=113mm
 Tightening torque
 terminal: 30Nm

EM 61536

d/19.05.16	Schr./File.	typelabel updated.	Danfoss Postaddress included		
c/25.03.13	Schr./Kor.	typelabel updated			
b/02.07.10	KOR/BRE	approval added			
a/13.01.10	KOR/BRE	part-no. added			
date	name	amendment			

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4,5
checked	18.11.09	Bremer	Bremer	format	A4
date		name	signature	DIN ISO 5456	

Dimensions B 0908115
 du/dt filter 443A - IP00

order number	130B2849	drawing number	Z790911020	modi.	d	sheet	1/1
Please observe protection clause to ISO 16016							