






12 11 10 9 8 7 6 5 4 3 2 1

Type	Value
IP Class	IP20
UL Type	Open
Enclosure Colour	red
Frame Size	CT 2









A ( 4 : 1 )



Dimension [mm]	Tolerances				
	<250	250>x>800	>800	parts in series	folded parts
Tolerance [mm]	+/-1	+/-2.5	+/-4	+/-2.5	+/-2.5

ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale		
			2:1		
	DATUM	Name			
	Gezeichnet	2022-10-13	FR		
	Kontrolliert			CT 2	
	Name				
				136c0112	
				REV	001
				Size A1	
Status	Änderungen	DATUM	Name	Sheet 1 of 4	
		3		2	1

12 11 10 9 8 7 6 5 4 3 2 1



Wire Bending space

Wire Bending space

ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			2:1	
Gezeichnet	DATUM	Name		
Kontrolliert	2022-10-13	FR		
Name			CT 2	
			136c0112	
Status	Änderungen	DATUM	Name	REV 001
				Size A1
			Sheet 2 of 4	

12

11

10

9

8

7

6

5

4

3

2

1

H

G

F

E

D

C

B

A

12

11

10

9

8

7

6

5

4

3

2



1

Sensor Terminal S1

Tool PH2 Torque 0.9Nm wire cross section 2.5mm<sup>2</sup>

Sensor Terminal S2

Tool PH2 Torque 0.9Nm wire cross section 2.5mm<sup>2</sup>



ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			1:2	
		DATUM	Name	
		Gezeichnet	2022-10-13	FR
		Kontrolliert		
		Name		
				CT 2
				136c0112
				REV 001
				Size A1
Status	Änderungen	DATUM	Name	Sheet 3 of 4
				2
				1