

REV	ECN	DATE
A	SP08066	10/08

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

DRN JNW
2/14/07
APR





NAME 208-600VOLT, 2C, CB
DRIVE FUSE, EMB1, FRAME B2-C1
D, V, D, T, C, M, S

PAGE 2 OF 2
SIZE A
DWG NO. 174U9431




CONTACT SEQUENCE CHART FOR S1
X INDICATES CONTACT CLOSED

POSITION	DRIVE	OFF	BYPASS
13-14			X
23-24	X		



CONTACT SEQUENCE CHART FOR S2
X INDICATES CONTACT CLOSED

POSITION	MOTOR 1	AUTO	MOTOR 2
11-12	X	X	
13-14		X	X
21-22		X	X
23-24	X		



EXTERNAL 24 V SUPPLY O.L. RELAY CONTACTS MK 107 D/O/B/T SWITCH

RESISTIVE LOAD 24 VDC, 1 A MAXIMUM

CONTACT CLOSED INDICATES MOTOR 1 SELECTED

RESISTIVE LOAD 24 VDC, 1 A MAXIMUM

CONTACT CLOSED INDICATES MOTOR ON BYPASS

RESISTIVE LOAD 24 VDC, 1 A MAXIMUM

CONTACT CLOSED INDICATES MOTOR ON DRIVE

RESISTIVE LOAD 24 VDC, 1 A MAXIMUM

CONTACT CLOSED INDICATES MOTOR 2 SELECTED

TEST CONNECTOR

FACTORY SETTING

WITHOUT CMS
WITH CMS

S105

CUSTOMER CONNECTIONS X55, X56 CLASS 2 POWER SOURCE REQUIRED FOR FIELD CONNECTION USE CLASS 1 CONDUCTORS CONDUCTOR SIZE 28-14 AWG