



FRAME SIZE B2			
VOLTAGE	HP	KW	
208/230	20	15	
460/600	30-40	22-30	

UNIT COOLING:  
 THE UNIT MUST BE INSTALLED VERTICALLY WITH THE MINIMUM FREE SPACE. ALL IP21/UL NEMA TYPE 1 AND IP54/NEMA TYPE 12 UNITS MAY BE MOUNTED SIDE BY SIDE WITH NO MINIMUM CLEARANCE.

- 1) 3X PLACE CONDUITS IN PRE-EXISTING CONDUIT HOLES
- 2) FOR NEMA TYPE 12 UNITS USE NEMA TYPE 12 CONDUITS AND HUBS

NOTICE:  
 THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES, AND SHALL BE RETURNED UPON REQUEST.

LATEST E.C.N. NO.: ECNSP07032	E.C.N. PRO-E ENTRY BY/DATE: KD 04/04/07	PRO-E ENTRY BY/DATE: KD 08/01/06	CHECKED BY/DATE: RD 05/03/07	DESIGNED BY/DATE: KD 08/01/06	APPROVAL:	ENG. APPROVAL BY/DATE: 5/1/07	TITLE: DWG, REF, SUBMITTAL, B2-TIER 1, P650
PLOT SCALE: NONE		PRO-E FILE: P404_B2_P650-2		SHEET: OF: DRAWING NO.:		SHEET: OF: DRAWING NO.:	
REV.:		REV.:		REV.:		REV.:	

**Danfoss**  
 DANFOSS DRIVES  
 4401 N. 36TH STREET, SUITE 200, WISCONSIN, WISCONSIN 53111 USA  
 (414) 251-5300 FAX: (414) 251-5300

17608474 B