





A B C D E F G H I J K L M N O P



- NOTES:
1. ALLOW 20" MINIMUM CLEARANCE ON LEFT SIDE OF ENCLOSURE.
  2. HATCHED AREA IS AVAILABLE FOR CONDUIT.
  3. ALLOW 30" MINIMUM CLEARANCE BETWEEN BACK OF ENCLOSURE AND OBJECTS OR WALLS BEHIND ENCLOSURE.
  4. ALLOW 18" MINIMUM CLEARANCE ON RIGHT SIDE OF ENCLOSURE.



REV	ECN	DATE	REV	ECN	DATE
7			3		
6			2		
5			1		
4			0		9/26/15

— NOTICE —  
 THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

DRN	APR	SUG
JUH		

TOLERANCE  
 Unless  
 Otherwise  
 Specified  
 2 PLC. ±.02  
 3 PLC. ±.005  
 SCALE 1.0

NAME  
**AQUA PHD PANEL, NON BYPASS,  
 500 - 600 HP / 480 VAC, OR 450 - 650 HP / 600 VAC, NEMA 3R,  
 DIMENSIONAL DWG.**

MODEL  
 FC-202

SHEET 1 OF 1

SIZE  
 D

DWG.  
 NO. 174N9336-04

MMW/akg, VMT