



FRAME SIZE	HP RANGE		
	204V	460V	600V
A2	0.5-3	0.5-5	-
A3	5	7.5-10	0.5-10

UNIT COOLING:
 THE UNIT MUST BE INSTALLED VERTICALLY WITH THE MINIMUM FREE SPACE. UL NEMA TYPE 12 UNITS MAY BE MOUNTED SIDE BY SIDE WITH NO MINIMUM CLEARANCE.

NOTICE:
 THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION HEREON SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. ALL RIGHTS ARE RESERVED AND NO PART OF THIS DOCUMENT OR ANY PART OF DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES, AND SHALL BE RETURNED UPON REQUEST.

PRO-E ENTRY BY/DATE: MN 11/03/08
 DESIGNED BY/DATE: MN 11/03/08
 APPROVAL: [Signature]

ENG. APPROVAL BY/DATE: 10/4/08
 TITLE: DWG, REF, SUBMITTAL, A2-A3
 SHEET: 1 OF 1
 DRAWING NO.: 177R0084

LATEST E.C.N. NO.: E.C.N. PRO-E ENTRY BY/DATE: PRO-E FILE: REV.:

DETAIL A
 SCALE 0.750

DETAIL B
 SCALE 0.750

DANFOSS DRIVES
 1235 23-0000 TEL: 0031 40000000
 1235 23-0000 TEL: 0031 40000000