




Side view, right




Front view



Side view, left



Top view



Name Plate



DECLARATION

1. Resistor
2. Terminal board, see detail view
3. Cable gland for load cables
4. Cable gland M16 thermo contact cable
5. Earthing bolt M6
6. Name plate / Warning signs
7. Front cover IP20
8. Rear cover IP20
9. Top cover IP20
10. Thermocontact 260 °C (NC)
11. Load connection, 2x bolt M8
12. Auxiliary connection for thermo contact, porcelain clamp 2,5"
13. 4x fixing hole Ø 9mm
14. Second cable gland (on demand)

CABINET TYPE: CM27

Danfoss code	Typecode	Ohm	cable gland type for load cables (3)	Weight [kg]	Center of mass [mm]		
					X	Y	Z
175U3085	MCE101C3R30P26KOE20BAW	3,3	2x M32	45	370	260	310
175U3089	MCE101C2R50P32KOE20BAW	2,5	2x M40	48	370	260	310
175U3093	MCE101C1R70P26KOE20BAW	1,7	2x M50	45	370	260	310
175U3097	MCE101C1R30P32KOE20BAW	1,3	2x M50	48	370	260	310
175U3205	MCE101C1R5P21KOE20BAW	15,5	M32	41	370	260	310
175U3208	MCE101C1R3P21KOE20BAW	13,5	M32	41	370	260	310
175U3209	MCE101C1R3P26KOE20BAW	13,5	M32	45	370	260	310
175U3211	MCE101C1R0P26KOE20BAW	11,0	M32	45	370	260	310
175U3213	MCE101C9R50P21KOE20BAW	9,5	M32	41	370	260	310
175U3216	MCE101C7R00P26KOE20BAW	7,0	M40	45	370	260	310
175U3241	MCE101C7R00P30KOE20BAW	7,0	M40	52	370	260	310

**Danfoss**  
Danfoss A/S  
Power Electronics Division  
Ulsmøse 1, 6300 Græsten  
Denmark

**MCE101 Brake resistor**  
xxR±10% IP20  
175C0610

Material: Cabinet material  
Zinc plated steel, without coating.  
Path:

Weight (g)	-	Date	14.03.2012	Creator:	F. Bülle	Approved:	H. Hansen	Scale	1:1
Tolerance:				File:	917CM27_02.dwg				
No.:	02	Last Revision:	13/637	Rev Date:	11.12.20132	By:	F. Bülle	Paper size:	A3

Drawing No.: 917CM27  
Sheet: 1 of 1