



- DECLARATION**
1. Resistor
 2. Terminal board, see Detail view
 3. Cable gland for load cables
 4. Cable gland M16 thermo contact cable
 5. Earthing bolt M10
 6. Name plate / Warning signs
 7. Front cover IP20
 8. Rear cover IP20
 9. Top cover IP20
 10. Thermocontact 260 °C (NC)
 11. Load connection, 2x bolt M8
 12. Auxiliary connection for thermo contact, porcelain clamp 2 5/8"
 13. 6x fixing hole Ø 9mm



Weight (g)	-	Date	14.03.2012	Creator:	F. Bülle	Approved:	H. Hansen	Scale	1:1
Tolerance:		Last Revision:	13/637	File:	917CMD37_02.dwg	Rev Date:	11.12.2013	By:	F. Bülle
No.:	02							Paper size:	A3

Danfoss
MCE101 Brake resistor
xxR±10% IP20
175C0627

Material: Cabinet material
 Path: Zinc plated steel, without coating.

Drawing No.: **917CMD37**
 Sheet: 1 of 1

CABINET TYPE: CMD37

Danfoss code	Typecode	Ohm	cable gland type for load cables (3)	Center of mass (mm)			Weight [kg]	Z
				X	Y	Z		
175U3220	MCE101C5R00P78K0E20BAW	5,0	2x M25	370	440	460	182	460
175U3222	MCE101C4R00P90K0E20BAW	4,0	2x M32	370	440	460	190	460
175U3228	MCE101C2R70P78K0E20BAW	2,7	2x M32	370	440	460	182	460
175U3230	MCE101C2R10P90K0E20BAW	2,1	2x M40	370	440	460	190	460