









Type	Value
Max Weight	225kg/496lb
IP Class	IP20
UL Type	Open




Position of Connectors	
A	Line
B	Motor
C	Brake / DC Terminals
D	Interface X0
E	Interface X1/X2
F	Grounding connections

1. MAX AIRFLOW (BACKCHANNEL) - 994m³/hr(585CFM)
2. MAX AIRFLOW (CABINET) - 660m³/hr(390CFM)

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL	-			
			1:20	A3	FINISH	-			
						DESCRIPTION	MCAD FA11 IP20		
CHANGED						DRAWING NUMBER	178R0008	REV	001
DESIGNED	Kishore 08/29/22					MODEL	MCAD FA11 IP20	SHEET	1 OF 2
CHECKED		PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.							

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF
CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	178R0008	REV	001
MODEL	MCAD FA11 IP20	SHEET	2 OF 2