










Type	Value
Max Weight	65 kg / 143 lb
IP Class	IP55/66
Nema Class	Type 12/4X



UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1$ MM (0,4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)			FIRST ANGLE PROJECTION	SCALE	SIZE	MATERIAL
				1:10	A3	
			FINISH			
			DESCRIPTION			
			MCAD FC C2 IP66 WITH DISCONNECT			
CHANGED						
DESIGNED	Danfoss	2015-04-23				
CHECKED						
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER	REV		
			MCAD-FC-C2-IP66-WITH-DISCONNECT	P1		
			MODEL	SHEET		
			C2-CUSTOMER-DRAWING	1 OF 2		

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL  
REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD-FC-C2-IP66-WITH-DISCONNECT	P1
MODEL	SHEET
C2-CUSTOMER-DRAWING	2 OF 2