





Type	Value
Max Weight	65 kg / 143 lb
IP Class	IP55/66
Nema Class	Type 12/4X





DETAIL C
SCALE 1:2



DETAIL B
SCALE 1:1




DETAIL A
SCALE 1:1



COOLING CLEARANCE

AIR SPACE INLET




AIR OUTLET

AIR INLET

SEE DETAIL C

SEE DETAIL A




SEE DETAIL B

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1\text{mm}$ (0,4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)			FIRST ANGLE PROJECTION	SCALE	SIZE	MATERIAL
				1:10	A3	
			FINISH			
			DESCRIPTION			
			MCAD FC C2 IP66 WO DISCONNECT			
CHANGED						
DESIGNED	Danfoss	2015-04-24				
CHECKED						
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER		REV	
			MCAD-FC-C2-IP66-WO-DISCONNECT		P1	
			MODEL		SHEET	
			C2-CUSTOMER-DRAWING		1 OF 2	



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL
REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD-FC-C2-IP66-WO-DISCONNECT	P1
MODEL	SHEET
C2-CUSTOMER-DRAWING	2 OF 2