






Type	Value
Max Weight	12 kg / 26.46 lb
IP Class	IP20
Nema Class	Chassis




DETAIL A
SCALE 1:1




DETAIL B
SCALE 1:1





MIN 200
[7.9]
COOLING CLEARANCE



AIR INLET ↑



MOUNTING BASE



MIN 200
[7.9]
COOLING CLEARANCE

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]			FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL	
				1:5	A3		
					FINISH		
					DESCRIPTION		
					MCAD H10 IP20		
CHANGED					DRAWING NUMBER		
DESIGNED	Danfoss	27-11-2015			MCAD-H10-IP20		REV
CHECKED					MCAD-H10-IP20		001
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			MODEL		SHEET		
			MCAD-H10-IP20		1 OF 1		

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.