




MR12 IS A COMBINATION OF 2 MR10

Item	Qty	Name	Part No
1	2	MR10_Collar_Plate	70CTC1107665
2	1	MR10_Collar_3	70CTC1107638
3	1	MR10_Collar_2	70CTC1107637

All dimensions are in Millimeters Unspecified tolerance according to: [Tolerance]		Projection	Size	A3	-	
Other dimensions acc. to 3D-model			Thickness	-	Material:	
Replace [Replace]			Mass	-	Kg	Finish:
Designer	Kishore	09-11-2021				Description / Name MR12 FLANGE MOUNTING
Modifier	[Modifier]	[Modifier Date]				
Confidential: Property of Danfoss and its subsidiaries. Not to be copied, handed over to or used by third party. Two- or three dimensional reproduction of content to be authorized by Danfoss Drives A/S					Item Number	REV
					DPD02220	AP1
						Sheet
						1 of 2



All dimensions are in Millimeters Unspecified tolerance according to: [Tolerance]	Projection 	Size	A3	Material: -
		Thickness	-	
		Mass/Prop/Max kg	-	
Other dimensions acc. to 3D-model		Description / Name		
Replace [Replace]		MR12 FLANGE MOUNTING		
Designer Kishore 09-11-2021		Item Number		
Modifier [Modifier] [Modifier Date]		DPD02220		
Confidential: Property of Danfoss and its subsidiaries. Not to be copied, handed over to or used by third party. Two- or three dimensional reproduction of content to be authorized by Danfoss Drives A/S				REV AP1 Sheet 2 of 2