




Side view, right




Front view



Side view, left




Name Plate




DECLARATION

1. Resistor
2. Terminal board, see detail view
3. Cable gland M25 for load cables
4. Cable gland M16 thermo contact cable
5. Earthing bolt M6
6. Name plate / Warning signs
7. Front cover IP20
8. Rear cover IP20
9. Top cover IP20
10. Thermocontact 260 °C (NC)
11. Load connection, 2x bolt M8
12. Auxiliary connection for thermo contact, porcelain clamp 2,5²
13. 4x fixing hole Ø 9mm

Top view



Detail view



Danfoss A/S
Power Electronics Division
Ulsmølle 1, 6300 Grøsten
Denmark

MCE101 Brake resistor
xxR±10% IP20
175C0637

Weight (g)	-	Date	14.03.2012	Creator:	F. Bülle	Approved:	H. Hansen	Scale	1:1
Tolerance:				File:	917CM13_03.dwg				
No.:	03	Last Revision:	13/637	Rev Date:	11.12.2013	By:	F. Bülle	Paper size:	A3

Danfoss code	175U3236	Typecode	MCE101C38R0P5K00E20BAW	Ohm	36	cable gland type for load cables (3)	M25	Weight [kg]	15	Center of mass [mm]	X	110	Y	260	Z	155
CABINET TYPE: CM13																
Material: Cabinet material Zinc plated steel, without coating.																
Path:																
Drawing No.: 917CM13																
Sheet: 1 of 1																