




TYPE APPROVAL CERTIFICATE
No. **ELE173322XG/004**

This is to certify that the product below is found to be in compliance with the applicable requirement of the RINA type approval system.

<i>Description</i>	FREQUENCY CONVERTERS
<i>Type</i>	Series FC-102
<i>Applicant</i>	DANFOSS POWER ELECTRONICS A/S ULSNAES 1 DK-6300 GRAASTEN DENMARK
<i>Manufacturer</i>	DANFOSS, LLC
<i>Place of manufacture</i>	4401 N. BELL SCHOOL RD., 61111 LOVES PARK (IL), U.S.A ULSNAES 1, DK-6300 GRAASTEN, DENMARK
<i>Reference standards</i>	Rules for the classification of ships.- Part C - Machinery, systems and fire protection. - Ch.3, Sect. 6, Table 1

Issued in **HAMBURG** on **November 16, 2022**. This Certificate is valid until **September 1, 2027**



RINA Services S.p.A.
Giuseppe Russo

This certificate consists of this page and 1 enclosure

TYPE APPROVAL CERTIFICATE

No. ELE173322XG/004

Enclosure - Page 1 of 4

Series FC-102

Product description:

The VLT[®] HVAC Drive Series FC-102 series are frequency converter for asynchronous motors for use in various marine applications.

FC-102: 200-240V

Power rating [kW]	Enclosure type			
	FC-102	IP20 (*1)	IP21 (*2)	IP55 (*3)
1,1	A2	A2 (*5)	A4+A5	A4+A5
1,5				
2,2				
3,0	A3	A3 (*5)	A5	A5
3,7				
5,5	B3	B1	B1	B1
7,5				
11				
15	B4	B2	B2	B2
18,5		C1	C1	C1
22	C3			
30				
37	C4	C2	C2	C2
45				

FC-102: 380-480/500V

Power rating [kW]	Enclosure type			
	FC-102	IP20 (*1)	IP21 (*2)	IP55 (*3)
1,1	A2	A2 (*5)	A4+A5	A4+A5
1,5				
2,2				
3,0				
4,0				
5,5	A3	A3 (*5)	A5	A5
7,5				
11	B3	B1	B1	B1
15				
18,5				
22	B4	B2	B2	B2
30				
37	C3	C1	C1	C1
45				
55				
75	C4	C2	C2	C2
90				

TYPE APPROVAL CERTIFICATE

No. ELE173322XG/004

Enclosure - Page 2 of 4

Series FC-102

FC-102: 525-690V

Power rating [kW]	Enclosure type			
	FC-102	IP20 (*1)	IP21 (*2)	IP55 (*3)
1,1	A3	NA	NA	NA
1,5				
2,2				
3,0				
3,7				
5,5				
7,5	B4	B2	B2	B2
11				
15				
18				
22				
30				
37	C3	C2	C2	C2
45				
55				
75	D3h			
90				

(*1) IP20/Panel mount. All IP20 versions can be upgraded to IP21 with optional kit

(*2) IP21/NEMA Type 1

(*3) IP55/NEMA Type 12

(*4) IP66/NEMA Type 4X

(*5) IP20/Panel with IP21 upgrade kit

FC-102: 380-480/500V

Power rating [kW]	Enclosure type				
	FC-102	6-pulse		12-pulse	Low Harmonic Drive (LHD)
		IP00 (*1)	IP20 (*1)	IP21 / IP54 (*2)	
110	NA	D3H	D1h/D5h/D6h	NA	NA
132					
160					
200	E2, E3h	E3h	D4h	E1/E1h	E9
250					
315					
355	E4h	E4h	F1/F3/E2h	F8/F9	F18
400					
450					
500	NA	NA	F1/F3	F10/F11	F18
560					
630					
710	NA	NA	F2/F4	F12/F13	NA
800					
1000					

TYPE APPROVAL CERTIFICATE

No. **ELE173322XG/004**

Enclosure - Page 3 of 4

Series FC-102

FC-102: 525-690V

Power rating [kW]	Enclosure type			
	6-pulse			12-pulse
FC-102	IP00 (*1)	IP20 (*1)	IP21 / IP54 (*2)	
75	NA	D3h	D1h/D5h/D6h	NA
90				
110				
132				
160				
200		D4h	D2h/D7h/D8h	
250				
315	E2, E3h	E3h	E1/E1h	F8/F9
400				
450				
500	E4h	E4h	F1/F3/E2h	F10/F11
560				
630				
710	NA	NA	F1/F3	F12/F13
800			F2/F4	
900				
1000				
1200				
1400				

(*1) IP00/IP20/Panel mount.

(*2) IP21/NEMA Type 1; IP54/NEMA Type 12

Technical data: (In accordance with Danfoss design guide)

Power supply: 200-240V / 380-480V / 525-690V, 50/60Hz

Voltage variation: +-10 %, -15% reduced power rating

Frequency variation: A, B and C frames: +-10%; D, E and F frames: +-5%

Output frequency: A, B and C frames: 0 - 590 Hz; D, E and F frames: 0 - 590 Hz

Temperature range in operation: 0 - 45°C, 46-55°C derating according to relevant design guide.

Protection class: IP00 / 20 / 21 / 54 / 55 / 66

Documents and drawings:

User manuals: - MG16O102 dated 01/2017; MG22A102 dated 01/2017; MG38A102 dated 01/2017;

Drawings: - 177r0659 dated 9/15/16; 177r0704 dated 06/24/2020; 177r0705 dated 06/24/2020; 177r0706 dated 06/24/2020;
- 177r0707 dated 06/25/2020;

Test reports:

Checklist for visual inspection 4001PRT2 00734665 Rev. 2.10 dated 2017-01-18;

Danfoss A/S: - 00715502 Rev. A dated 2013-07-30; 00734306 Rev. A dated 2017-01-12; 00734307 Rev. A dated 2017-01-13;

- 00734308 Rev. A dated 2017-01-13; 00734309 Rev. A dated 2017-01-13; 00734724 dated 2017-01-26;

- 00735629 Rev. A dated 2017-03-16; 00735840 dated 2017-03-27; P4001 dated 3/15/2017;

- P4001 Rev. A dated 2017-01-10; P7020 dated 2015-07-10; tr4001 dated 12-09-16; PEC-4639 dated 19-10-2021; PEC-4640 dated

24-09-2021; PEC-4679 dated 28-09-2021; PEC-4680 dated 05-10-2021; PEC-4681 dated 13-10-2021; PEC-4682 dated 15-10-2021;

Datasyst Engineering & Testing Services Inc.: - D15-15766 Rev. A dated July 29,2013; D15-17445 dated August 17,2016;

Elite Electronic Engineering Inc.: - 1604970-01 Rev.B dated January 17, 2017;

TÜV Rheinland: - 19645766001 dated 11 Jan 2017; 19645767001 dated 11 Jan 2017;

UL: - 00733941; 11494250A dated December 16,2016; 11494250B dated December 16,2016;

- 4786962025-S1-1 dated 9 July 2015; Break Down of Component_Test DataSheet;

TYPE APPROVAL CERTIFICATE

No. **ELE173322XG/004**

Enclosure - Page 4 of 4

Series FC-102

Manufacturing sites:

DANFOSS, LLC
4401 N. BELL SCHOOL RD.
61111 LOVES PARK (IL)
U.S.A.

DANFOSS DRIVES A/S
ULSNAES 1
6300 GRAASTEN
DANMARK

Remarks:

- The products fulfill EC-Code: EC21.
- All changes in software are to be recorded as long as the system is in use on board. Major changes in the software are to be approved before being installed in the converter.
- Converters EMC classed C3 according to IEC 61800-3 can be installed in "special distribution zone" and "general power distribution zone" in accordance with IEC 60533 provided precautions are taken to attenuate these effects on the distribution system, so the safe operation is assured.

This certificate replaces and annuls the previous certificate ELE173322XG/001.

HAMBURG November 16, 2022

