


Flow Control Valves Catalog

Catalog HIC 2F95-01

OPERATION


This valve is an adjustable, priority-type, pressure compensated flow control valve.

Schematic



SPECIFICATIONS

Theoretical performance



Specifications

Rated pressure	210 bar 3000 psi	
Max regulated flow	60 l/min 16 US gal/min	
Max inlet flow	95 l/min 25 US gal/min	
Weight	1.00 kg 2.20 lb	
Cavity	none	

DIMENSIONS

Cross-sectional view

