



### OPERATION

Solenoid Valve, Spool Type, 2-Position, 4-Way, 10-size. When de-energized, the HSV10-24-01 allows flow from port 3 to port 2, and from port 4 to port 1. When energized, the spool shifts to allow flow from port 3 to port 4, and from port 2 to port 1. Follow the "Operating Envelope" limits to ensure shifting of the valve during operation.



### APPLICATIONS


These spool-type valves are primarily used in mobile and industrial applications for blocking the flow of a 2-way function, pump unloading or cylinder regeneration. Solenoid spool-type valves are direct acting and respond quickly to coil voltage input. Spool valves will have some leakage due to spool clearance, so if your application requires no leakage at the working port(s), apply a low leakage poppet valve(s), like PO check valve, counterbalance valve, etc., in addition to this solenoid valve.

### SPECIFICATIONS

Rated pressure*	350 bar [5075 psi]*
Rated flow at 7 bar [100 psi]	25 l/min [6.6 US gal/min]
Weight	0.45 kg [0.99 lb]
Cavity	SDC10-4
Standard Coil	H16 29Watt


\* Rated Pressure based on NFPA fatigue test standards (at 1 Million Cycles).

### SCHEMATIC




### PERFORMANCE CURVES

Pressure drop  
26 cSt [121 SUS] hyd.oil at 50°C [122 °F]



Operating envelope






# Solenoid Valves Catalog

## 4-Way, 2-Position Spool

### HSV10-24-01




### DIMENSIONS



### EXAMPLE CIRCUITS

Motor directional control



### ORDERING INFORMATION

**HSV10 - 24 - 01 - H12D - DE - XC - P - 00**

High Pressure Solenoid Valve,  
This is a direct-acting, 2-position,  
4-way, spool-type solenoid valve.

#### Coil Voltage

Code	Description
H00	No Coil
H12D	12 VDC
H24D	24 VDC

#### Coil Termination

Code	Description	IP Rating
00	No Coil	-
FL	Flying Lead	IP 69k
DE	Deutsch	IP 69k
AS	AMP SuperSeal 1.5 and Metri-Pack 150 type 1	IP 69k
ASDB	AMP Super Seal with Diode Bidirectional	IP 69k
DEDB	Deutsch with Diode Bidirectional	IP 69k
FLDB	Flying Lead with Diode Bidirectional	IP 69k

#### Bodies

Code	Port & Material	Body Nomenclature
00	Cartridge only	No Body
S3B	3/8 BSP, Ductile	SDC10-4-S3B
S4B	1/2 BSP, Ductile	SDC10-4-S4B
S6S	#6 SAE, Ductile	SDC10-4-S6S
S8S	#8 SAE, Ductile	SDC10-4-S8S

\*\*\* Aluminium bodies available for lower pressure application. Please consult factory for details.

#### Seal Option

Code	Seal Material	Seal kit
P	Polyurethane Single Seal	11143824

#### Manual Override

Code	Description
XC	No Manual Override

SV - Solenoid Valves  
HSV10-24-01