









Type	Value
Max Weight	139kg/306lb
IP Class	IP21
UL Type	Type I




Position of connectors	
A	Line
B	Motor
C	Interface X0
D	Interface XI/X2
E	Grounding connections

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

1. MAX AIRFLOW (BACKCHANNEL) - 638m<sup>3</sup>/hr (375CFM)
2. MAX AIRFLOW (CABINET) - 204m<sup>3</sup>/hr (120CFM)

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±0.1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL	-	
			1:4	A3	FINISH	-	
						DESCRIPTION	
CHANGED						MCAD FK10a IP21	
DESIGNED	Kishore 05/22/23						
CHECKED				DRAWING NUMBER	178r0021	REV	001
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				MODEL	MCAD FK10a IP21	SHEET	1 OF 3






THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF  
CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	178r0021	REV	001
	MCAD FK10a IP21	SHEET	2 OF 3

Optional Floor mounting with Pedestal

Standard  
(Without Pedestal option)



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF  
CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	178r0021	REV	001
MODEL	MCAD FK10a 1P21	SHEET	3 OF 3