



**Danfoss A/S**

DK-6430 Nordborg  
Denmark  
CVR nr.: 20 16 57 15

Telephone: +45 7488 2222  
Fax: +45 7449 0949

# EC/EU DECLARATION OF CONFORMITY

## Danfoss A/S

Danfoss Power Solutions, Connect & Control Solutions

declares under our sole responsibility that the

Product(s): **Telematics**

Type(s): **IoT Gateway**

Models(s): **CS10, BT510**

Software: **Danfoss Plus+1**

Covered by this declaration is (are) in conformity with the following directive(s), standard(s), or other normative document(s), provided that the product is used in accordance with our instructions.

- EMC Directive 2014/30/EU
- RoHS2 Directive 2011/65/EU including amendment 2015/863  
EN 50581:2012 Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances
- Radio Equipment Directive 2014/53/EU
  - Article 3.1a: EN 62368-1:2014/A11:2017  
EN 60950-22:2017
  - Article 3.1b: EN 301 489-1 V2.2.2:2019  
EN 301 489-17 V3.2.0:2017
  - Article 3.2: EN 300 328 V2.1.1:2016  
EN 300 440 V2.1.1:2017  
EN 301 893 V2.1.1:2017
- Low Voltage Directive 2014/35/EU

**Additional information:**

The product was tested in typical configurations.

All models in this document have been individually tested for conformity.

Year for first CE-marking: 2020

Date 7/9/20	Issued by: Adam Gibson Signature 	Date 7-10-20	Approved by: Joe Schottler Signature 
	Title Test Engineer Place of issue: Minneapolis, Minnesota		Title Senior Director of Engineering Place of approval: Minneapolis, Minnesota

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation



**Danfoss A/S**

DK-6430 Nordborg  
Denmark  
CVR nr.: 20 16 57 15

Telephone: +45 7488 2222  
Fax: +45 7449 0949

Product(s): **Telematics**  
Type(s): **IoT Gateway**  
Models(s): **CS10, BT510**

**Frequency Band:**

2.400 – 2.4835 GHz  
U-NII-1 (5.150 – 5.250 GHz)  
U-NII-3 (5.725 – 5.825 GHz)

**Max Output Power:**

16dBm  
16dBm  
10dBm

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation