

additional informations:
 filter colour : RAL7001
 filter weight : 12,9kg
 cable clamp : 2x 195N3206

label:

VLT MCC 101 sine wave FILTER
 www.danfoss.com

TTC: MCC101A10KCTE20B S.N.: 000167-188
 P.N.: 130B7324
 3x 525-850V - 50/60Hz (max 100Hz)
 3x 10A@50Hz 5A@60Hz 7A@100Hz
 chassis IP20 Temp. 45°C@15°C

130B7324000167-188

Use only with a type 1 or type 2 SPD overvoltage control device

E219022
 Int. Cont. Eq. -HDI
 B 1212047.1 FA-Nr.: 000000
 See manual for
 UL-requirements

MADE IN GERMANY
 L=8,1mm
 Dy=3,5mm
 P=4x4mm
 Weight: 12,9kg
 Tightening torque
 terminal: 0,5-1,0Nm
 only CU

EN 61558 **CE**

c|04.05.16| Schr./Fie. | typeable updated, Danfoss Postaddress included
 b|21.06.15| Schr./Fie. | typeable updated
 a|17.11.14| Schr./Fie. | typeable updated
 | date | name | amendment

Dimensions toleranced according to ISO 2768-m

Tolerance class	0.5 to 3	3 to 6	6 to 30	30 to 120	120 to 400	400 to 1000
from	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8





drawn	19.02.13	Kornau	Kornau	scale	1:4
checked	19.02.13	Bremer	Bremer	format	A4
date				signature	

Dimensions B 1212047.1
 sine wave filter 690V 10A – IP20

order number	130B7324	drawing number	Z791302004	modi.	C	sheet	1/2
--------------	----------	----------------	------------	-------	---	-------	-----

Please observe protection clause to ISO 16016

included accessories
(screen connection plate)



c 04.05.16 Schr./File.	type/label updated.	Danfoss Postaddress included
b 21.06.15 Schr./File.	type/label updated	
a 17.11.14 Schr./File.	type/label updated	
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	19.02.13	Kornau	Kornau	scale	1:4
checked	19.02.13	Bremer	Bremer	format	A4
date		name	signature	DIN ISO 5456	

all dimensions mm	
-------------------	--

Dimensions B 1212047.1			
sine wave filter 690V 10A – IP20			
order number	130B7324	drawing number	Z791302004
Please observe protection clause to ISO 16016			modi: C
			sheet 2/2

1 2 3 4 5 6 7 8