





Type	Value
Max Weight	55kg/121lb
IP Class	IP20
Nema Class	Open

EARTHING INFORMATION



200mm Air space for cooling

Product name




Danger label

200mm Air space for cooling


Detailed earthing information SEE DETAIL C

128 [5]


336 [13.2]



Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2



UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 0.1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]



SCALE 1:10

DRAWING SIZE A3

MATERIAL	-
FINISH	-

CHANGED		
DESIGNED	Danfoss	10/07/21
CHECKED		



DESCRIPTION	
MCAD FA08 IP20	

PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	MCAD FA08 IP20	REV	P1
MODEL	MCAD FA08 IP20	SHEET	1 OF 1

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.