

Flow Control Valves Catalog

Fixed Setting, Priority Type CP310-1

OPERATION


This valve is a fixed, pressure compensated priority-type flow control valve.

Schematic ① ③

(2)

SPECIFICATIONS

Theoretical performance




Specifications

| Rated pressure | 210 bar [3000 psi] |
|--------------------|----------------------|
| Max regulated flow | 23 l/min |
| | [6 US gal/min] |
| Max inlet flow | 38 l/min |
| | [10 US gal/min] |
| Weight | 0.13 kg [0.29 lb] |
| Accuracy ± 20% | 0.4-2.2 l/min |
| | [0.1-0.6 US gal/min] |
| ± 15% | 2.3-6.8 l/min |
| | [0.6-1.8 US gal/min] |
| ± 10% | 6.9-22.7 l/min |
| | [1.8-6 US gal/min] |
| Cavity | SDC10-3 |

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

