


## Cartridge Valves Technical Information Motor Mount HICs MM-DH-00-SVP10-NCR

#### **OPERATION**

This is a bypass solenoid HIC with drain that mounts to DH motors with manifold mount porting. When energized, the valve connects ports A and B. Drain connects to port A.

#### Schematic



P104 750

#### **SPECIFICATIONS**

#### Theoretical performance

Pressure drop

33 cSt [154 SUS] hyd.oil @ 38°C [100° F] psi bar 261 18 218 15 1 to 2 174 12 De-energized 131 9 2 to 1 87 6 Energized 44 3 lο 20 30 40 50 60 70 2.6 5.3 7.9 10.6 13.2 15.9 18.5 US gal/min P103 626E


#### **Specifications**

specifications.	
Rated pressure	210 bar [3045 psi]
Rated flow at 7 bar	80 l/min [21 US gal/min]
[102 psi]	
Leakage	6 drops/min @ at rated
	pressure
Weight	1.36 kg [3.00 lb]
Cartridge	SVP10-NCR
Shuttle/drain port	#4 SAE (1/4 BSP)
Service mount kit	11023864
Motor	DH

#### **DIMENSIONS**

#### Cross-sectional view

### mm [in]



# ORDERING INFORMATION

