

Dimensions


mm [in]

TOLERANCES UNLESS OTHERWISE SPECIFIED

Diameter and Lengths:
 if < 18mm ± 0.1 [0.004]
 Angles ± 2°

	Ø0.05 [0.002]	A
	0.025 [0.001]	B

1.6 [63]



CA - Cavities
 SDC10-2

Form tools

	Model code	Material number
Finishing tool	SDC-10-2-FT	11027186
Roughing tool	SDC-10-2-RT	11027187

Housings

Order Code	Description	Ports	Page
CP10-2-10S-2CR	Aluminum Housing	SAE #10	-
CP10-2-6S	Aluminum Housing	SAE #6	HS - 80
CP10-2-8S	Aluminum Housing	SAE #8	HS - 80
CP10-2-8S-2PL	Parallel housing	SAE #8	-
CP10-2-S6S	Steel Housing	SAE #6	HS - 80
CP10-2-S8S	Steel Housing	SAE #8	HS - 80
SDC10-2-DG-3B	Aluminum Housing	3/8 BSP	-
SDC10-2-DG-4B	Aluminum Housing	1/2 BSP	-
SDC10-2-LG1-4B	Aluminum Housing, Two #2 Ports	1/2 BSP	HS - 81
SDC10-2-LG2-4B	Aluminum Housing, Two #1 Ports	1/2 BSP	HS - 82