



FRAME SIZE B1		
VOLTAGE	HP	KW
208/230	7.5-15	5.5-11
460/600	15-25	11-18.5

UNIT COOLING:
 THE UNIT MUST BE INSTALLED VERTICALLY WITH THE MINIMUM FREE SPACE. ALL IP21/UL NEMA TYPE 1 AND IP54/NEMA TYPE 12 UNITS MAY BE MOUNTED SIDE BY SIDE WITH NO MINIMUM CLEARANCE.

- 1) 3X PLACE CONDUITS IN PRE-EXISTING CONDUIT HOLES
- 2) FOR NEMA TYPE 12 UNITS USE NEMA TYPE 12 CONDUITS AND HUBS

NOTICE:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION CONTAINED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. IT SHALL NOT BE USED OR CAUSED TO BE USED IN ANY MANNER THAT COULD BE REPRODUCED OR COPIED IN WHOLE OR IN PART OR DISCLOSED, EITHER ORALLY OR IN WRITING, WITHOUT THE EXPRESS WRITTEN PERMISSION OF DANFOSS DRIVES, AND SHALL BE RETURNED UPON REQUEST.

LATEST E.C.N. NO.: ECNSP07032		E.C.N. PRO-E ENTRY BY/DATE: KD 04/04/07		PLOT SCALE: NONE		PRO-E FILE: P404.B1.P650-2	
PRO-E ENTRY BY/DATE: KD 08/01/06		CHECKED BY/DATE: PD 09/03/07		DESIGNED BY/DATE: KD 08/01/06		MFG. APPROVAL BY/DATE:	
APPROVAL:		ENG. APPROVAL BY/DATE: S/7/07		TITLE: DWG, REF, SUBMITTAL, B1-TIER 1, P650		SHEET: 1 OF 1	
DRAWING NO.: 17608471		REV.: B		DANFOSS DRIVES 440 N. BELL ST. P.O. BOX 244, ILWACO, OR 97111 USA (503) 535-8800 FAX (503) 535-8888			