

ENGINEERING
TOMORROW




Installation guide

Clone Test

1 UAT Test Chapter

1.1 UAT Test Electrical Wiring

Illustration 1: Basic Wiring Schematic Drawing



⚠ NOTICE ⚠

There is no access to UDC- and UDC+ on the following units:

- IP20, 380–480 V, 30–90 kW (40–125 hp)
- IP20, 200–240 V, 15–45 kW (20–60 hp)
- IP20, 525–600 V, 2.2–90 kW (3–125 hp)
- IP54, 380–480 V, 22–90 kW (30–125 hp)

1.1.1 UAT Test Body Text

1.2 UAT Test Body Text

1.3 UAT Test Task

1. What's the task
2. Define the task
3. @klækæ™

Example:


jkljklæjækl

1.4 UAT Test Concept

1.5 Test Chapter Level 2

1.5.1 UAT Test Electrical Wiring

Illustration 2: Basic Wiring Schematic Drawing



▲ NOTICE ▲

There is no access to UDC- and UDC+ on the following units:

- IP20, 380–480 V, 30–90 kW (40–125 hp)
- IP20, 200–240 V, 15–45 kW (20–60 hp)
- IP20, 525–600 V, 2.2–90 kW (3–125 hp)
- IP54, 380–480 V, 22–90 kW (30–125 hp)

1.5.1.1 UAT Test Body Text

1.6 Math ML Test

$$a \neq a \times \frac{b^2}{c}$$

ENGINEERING
TOMORROW

Danfoss

.....
Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.
.....

Danfoss A/S
Ulsnaes 1
DK-6300 Graasten
vlt-drives.danfoss.com

