




1) PLACE CONDUITS IN MARKED AREA.  
2) FOR NEMA TYPE 12 UNIT USE NEMA TYPE 12 CONDUITS AND HUBS.



DETAIL A  
SCALE 0.250



DETAIL B  
SCALE 0.250



DETAIL C  
SCALE 0.250

| FRAME SIZE CI |       |         |  |
|---------------|-------|---------|--|
| VOLTAGE       | HP    | KW      |  |
| 208/230       | 25-40 | 18.5-30 |  |
| 460/600       | 50-75 | 37-55   |  |

UNIT COOLING:  
THE UNIT MUST BE INSTALLED VERTICALLY WITH THE MINIMUM FREE SPACE. ALL IP21/UL NEMA TYPE 1 AND IP54/NEMA TYPE 12 UNITS MAY BE MOUNTED SIDE BY SIDE WITH NO MINIMUM CLEARANCE.

**-NOTICE-**  
THIS DRAWING IS PROPRIETARY AND SHALL NOT BE COPIED OR ITS CONTENTS DISCLOSED TO OUTSIDE PARTIES WITHOUT THE WRITTEN CONSENT OF THE TRANE COMPANY

|   |  |  |                                       |
|---|--|--|---------------------------------------|
| LATEST E.C.N. NO.:<br>E.C.N. PROJ. E-ENTER BY/DATE:<br>PLOT SCALE: NONE | PRO-E ENTER BY/DATE: MN 10/20/08<br>DESIGNED BY/DATE: MN 10/20/08<br>APPROVAL: | CHANGED BY/DATE: <i>01/10/09</i><br>DWG. APPROVAL BY/DATE: | TITLE: DWG. REF. SUBMITTAL, CI-TIER 1 |
| THE TRANE COMPANY<br>A DIVISION OF<br>AMERICAN STANDARD INC.            | SHEET: 1 OF 1<br>DRAWING NO.: 174N3467   | REV.:  |                                       |