


01  
02  
03  
04  
05  
06  
07  
08  
09  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
21  
22  
23  
24  
25  
26  
27  
28  
29  
30  
31  
32  
33  
34  
35  
36  
37

A B C D E F G H I J K L M M O P

| DRIVE PARAMETERS |                   |         |                      |
|------------------|-------------------|---------|----------------------|
| PARAMETER #      | NAME              | SETTING | VALUE                |
| 0-03             | REGIONAL SETTINGS | 1       | NORTH AMERICA        |
| 5-01             | TERMINAL 27       | 1       | OUTPUT               |
| 5-02             | TERMINAL 29       | 2       | OUTPUT               |
| 5-11             | TERMINAL 19       | 52      | RUN PERMISSIVE       |
| 5-14             | TERMINAL 32       | 7       | EXTERNAL INTERLOCK   |
| 5-15             | TERMINAL 33       | 37      | FIRE MODE            |
| 5-30             | TERMINAL 27       | 188     | FILTER CAP CONNECT   |
| 5-31             | TERMINAL 29       | 5       | RUNNING              |
| 5-40(0)          | RELAY 1           | 160     | NO ALARM             |
| 5-40(1)          | RELAY 2           | 167     | START COMMAND ACTIVE |

- NOTES:
- \* INDICATES COMPONENTS NOT SUPPLIED BY FACTORY.
  - FEEDER CIRCUIT PROTECTION AND INPUT AND MOTOR WIRING MUST BE SELECTED IN ACCORDANCE WITH THE N.E.C. ANY APPLICABLE LOCAL CODES AND THE DRIVE PANEL NAMEPLATE RATING. DANFOSS RECOMMENDS AN INSULATED BONDING WIRE FROM MOTOR TO DRIVE RUNNING WITH MOTOR LEADS INSIDE CONDUIT OR SHIELDED CABLE.
  - REPLACE JUMPER WITH N.C. SAFETY INTERLOCK CONTACT AS APPLICABLE.
  - REFER TO THE INSTALLATION OPERATION MANUAL FOR THE PROPER DRIVE FUSING. DRIVE FUSES ARE INTERNAL TO DRIVE ON UNITS > 125 HP.
  - JUMPER FROM H2 TO H3 IS NOT PRESENT ON TRANSFORMER PRIMARY FOR 575V INPUT.
  - MOTOR/LINE AND CONDUIT GROUND CONNECTIONS TO BE MADE ON CABINET GROUND BAR.



NOTE: ALL DRIVE WIRES #18 AWG BLUE UNLESS OTHERWISE NOTED  
NOTE: ANALOG PAIRS ARE 18 AWG BELDEN #9460

|             |  |  |  |   |     |      |     |                             |           |                                   |       |                                       |              |        |                   |
|-------------|--|--|--|---|-----|------|-----|-----------------------------|-----------|-----------------------------------|-------|---------------------------------------|--------------|--------|-------------------|
|             |  |  |  | - NOTICE -  |     | DRN  |     | TOLERANCE                   |           | NAME                              |       | <i>Danfoss</i>                        |              |        |                   |
|             |  |  |  | THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST. |     | SJK  |     | Unless Otherwise Specified  |           | POWER DISTRIBUTION WIRING DIAGRAM |       |                                       |              |        |                   |
|             |  |  |  |   |     | APR  |     | 2 PLC. ±.02<br>3 PLC. ±.005 |           | MODEL                             |       | PHD PANEL HVAC NON-BYPASS 460/575 VAC |              |        |                   |
| DESCRIPTION |  |  |  | REV   | ECN | DATE | SJK |                             | SCALE 1.0 |                                   | FC102 |                                       | SHEET 1 OF 1 | SIZE D | DWG. NO. 174N9951 |