



CERTIFICATE NUMBER 15-LD1432892-1-PDA-DUP  
EFFECTIVE DATE 09-May-2016  
EXPIRATION DATE 19-Jan-2021  
ABS TECHNICAL OFFICE London

## CERTIFICATE OF Product Design Assessment

This is to certify that a representative of this Bureau did, at the request of

### **VACON (CHINA) DRIVES CO. LTD HAIYAN BRANCH**

located at

**BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY,  
JIAXING CITY, ZHEJIANG PROVINCE, P.R. CHINA, JIAXING, China, 314300**

assess design plans and data for the below listed product. This assessment is a representation by the Bureau as to the degree of compliance the design exhibits with applicable sections of the Rules. This assessment does not waive unit certification or classification procedures required by ABS Rules for products to be installed in ABS classed vessels or facilities. This certificate, by itself, does not reflect that the product is Type Approved. The scope and limitations of this assessment are detailed on the pages attached to this certificate.

**Product** Frequency Converter


**Model** VACON 100 and 100X AC Drives

This Product Design Assessment (PDA) Certificate remains valid until 19-Jan-2021 or until the Rules and/or Standards used in the assessment are revised or until there is a design modification warranting design reassessment (whichever occurs first).

Acceptance of product is limited to the "Intended Service" details prescribed in the certificate and as per applicable Rules and Standards.

This Certificate is valid for installation of the listed product on ABS units which exist or are under contract for construction on or previous to the effective date of the ABS Rules and standards applied at the time of PDA issuance. Use of the Product for non-ABS units is subject to agreement between the manufacturer and intended client.

American Bureau of Shipping

  
Theodoros Chatzgakaidas, Senior Engineer

NOTE: This certificate evidences compliance with one or more of the Rules, Guides, standards or other criteria of ABS or a statutory, industrial or manufacturer's standards. It is issued solely for the use of ABS, its committees, its clients or other authorized entities. Any significant changes to the aforementioned product without approval from ABS will result in this certificate becoming null and void. This certificate is governed by ABS Rules 1-1-A3/5.9 Terms and Conditions of the Request for Product Type Approval and Agreement (2010)



VACON (CHINA) DRIVES CO. LTD. HAIYAN BRANCH  
BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, P.R. CHINA  
JIAXING ZHEJIANG  
China 314300  
Telephone: 18121589808/021-6153000  
Fax: 02-61513100  
Email: leo.sun@danfoss.com  
Web: www.danfoss.cn

Tier: 5 - Unit Certification Required TC

**Product:** Frequency Converter  
**Model:** VACON 100 and 100X AC Drives  
**Intended Service:**

For use on ABS Classed Vessels and Offshore Facilities in accordance with the listed ABS Rules and International Standards.

**Description:**

VACON100 and 100X AC Drive are the drives for controlling various type of motors.

**Rating:**

VACON 100

Frame sizes MR4 to MR12

POWER: 0.37 kW to 800 kW

Supply Voltage: 3~AC,208-690V, 47-65 Hz.

Output Frequency: 0-320Hz (standard)

Continuous Current (Low overload): 3.4 to 1180 Amps

Input current ((Low overload): 3.2 to 1164 Amps

Continuous Current (high overload): 2.6 to 920 Amps

Input current (high overload): 2.4 to 908 Amps

Ambient temperature: IL : -10°C (-14°F) (no frost)... +40°C (104°F) and IH: -10C (-14°F)(no frost)... +50°C (122°F)

Degree of protection: IP54.

Option : IP21 drives for controlled environment, IP00 for frames MR8, MR9, MR10 and MR12 are optional variant for system integrators which would like to use their own cabinet type.

Vacon 100 is ATEX certified. EC-Type Certificate Ref : VTT 06 ATEX 048X Issue 2, Marking : EX II (2) GD

VACON 100X

Frame sizes MM4 to MM6

POWER: 1.1 kW to 37 kW

Supply Voltage: 3~AC,208 to 240V (50/60Hz) or 380 to 480(500)V (47.5 - 66Hz).

Output Frequency: 0-320Hz (standard)

rated Continuous Current: 3.4 to 72 Amps.

Input current: 3.4 to 67.5 Amps.

Ambient temperature -10 c to +50 C degrees (the output current must be derated to 75% of In).

Degree of protection: IP66.

**Service Restriction:**

Unit Certification is required for semiconductor converters used to control motor drives having a rated power of 100 kW(135 hp) or over that are intended for essential services as 4-8-3/1.5 of Steel Vessels Rules (2016). Detailed requirements for unit certification are in 4-8-3/8.7 of the ABS Rules for Building and Classing Steel Vessels 2016.

Environmental tests and approval are for hardware only.

When incorporated in a system of Category I, II or III in accordance with 4-9-3/7.1 and 4-9-3/Table 1 of the ABS Rules for Building and Classing Steel Vessels 2015 the documentation detailed in 4-9-3/Table 2 is to be submitted to ABS or to be available for review by ABS as applicable.

If the manufacturer or purchaser request an ABS Certificate for compliance with a specification or standard, the specification or standard, including inspection standards and tolerances, must be clearly defined.

**Comments:**

The Manufacturer has provided a declaration about the control of, or the lack of Asbestos in this product.

Arrangements and details are required to be submitted and reviewed by ABS for compliance with all other applicable Rule requirements prior to each such installation on board an ABS classed vessel.

Where used in machinery space (i.e. engine room, boiler room) the units are to have an ambient rating of 45°C.



**VACON (CHINA) DRIVES CO. LTD. HAIYAN BRANCH**

BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, P.R. CHINA

JIAXING ZHEJIANG

China 314300

Telephone: 18121589808/021-6153000

Fax: 02-61513100

Email: leo.sun@danfoss.com

Web: www.danfoss.cn

**Tier: 5 - Unit Certification Required TC**

The units are to have the appropriate enclosure IP rating as per 4-8-3/Table 2 based on their installed location. Details related to overload protection, running protection and motor starter disconnects are to be submitted for each installation.

Each installation of the specific VACON100 & 100X AC Drive on board an ABS classed vessel is to be provided with main cables and fuses which sizes are as recommended by VACON (referenced in vacon 100 ac drives installation manual enclosed drives, Doc ID. DPD01666B).

We note that MR8, MR9, MR10 and MR12 are delivered as IP00 modules and they do not comply with EMC requirement as per 4-9-7/Table 9 of the Rules for Building and Classing Steel Vessels. Planned EMC measures are required to be submitted for review prior to installation of these models on board.

Only Vacon 100 is ATEX certified. Vacon 100X is not ATEX certified as it is motor mountable.

ATEX certified equipment is not to be installed in hazardous areas on U.S. Flagged Vessels, unless it can be proven to have been tested to the IEC 60079 series standards by an independent laboratory accepted by the U.S. Coast Guard. USCG MI Notice 01-12 (February 7, 2012).

**Notes/Drawing/Documentation:**

- Drawing No. 01/205/5216/12, TYPE EXAMINATION CERTIFICATE, Revision: -, Pages: 1
- Drawing No. 028-713010338-000, TECHNICAL REPORT, Revision: 00, Pages: 1
- Drawing No. 028-71395934-000, TECHNICAL REPORT, Revision: 00, Pages: 1
- Drawing No. 028-71397706-000, TECHNICAL REPORT, Revision: 00, Pages: 1
- Drawing No. 18690, INVESTIGATION REPORT, Revision: -, Pages: 1
- Drawing No. 18701, INVESTIGATION REPORT, Revision: -, Pages: 1
- Drawing No. D8 12 02 76674 005, COMPLIANCE DOCUMENT, Revision: -, Pages: 1
- Drawing No. D8 12 02 76674 006, COMPLIANCE DOCUMENT, Revision: -, Pages: 1
- Drawing No. E8N 13 02 76674 009, ATTESTATION OF COMPLIANCE, Revision: -, Pages: 1
- Drawing No. EC DECLARATION OF CONFORMITY, EC DECLARATION OF CONFORMITY, Revision: -, Pages: 1
- Drawing No. FI 6982, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 6983, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 6984, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 7019, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 7020, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 7021, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 7108, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8646 M1, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8652 M1, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8653 M1, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8744, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8745, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8746, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8747, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI 8748, CB TEST CERTIFICATE, Revision: -, Pages: 1
- Drawing No. FI12/0025, SYSTEM CERTIFICATION, Revision: -, Pages: 1
- Drawing No. FI12/1010, SYSTEM CERTIFICATION, Revision: -, Pages: 1
- Drawing No. FI12/2004, SYSTEM CERTIFICATION, Revision: -, Pages: 1
- Drawing No. MM4 MAIN BLOCK DIAGRAM, VACON 100X MM4 208 - 500V MAIN BLOCK DIAGRAM, Revision: A, Pages: 1
- Drawing No. MM4 STANDARD LEVEL MAIN CIRCUIT DIAGRAM, VACON 100X MM4 208-500V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: A, Pages: 1
- Drawing No. MM5 MAIN BLOCK DIAGRAM, VACON 100X MM5 208-500V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: A, Pages: 1
- Drawing No. MM5 STANDARD LEVEL MAIN CIRCUIT DIAGRAM, VACON 100X MM5 208-500V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: A, Pages: 1



**VACON (CHINA) DRIVES CO. LTD. HAIYAN BRANCH**

BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, P.R. CHINA

JIAXING ZHEJIANG

China 314300

Telephone: 18121589808/021-6153000

Fax: 02-61513100

Email: leo.sun@danfoss.com

Web: www.danfoss.cn

**Tier: 5 - Unit Certification Required** TC

Drawing No. MM6 MAIN BLOCK DIAGRAM, VACON 100X MM6 208 - 500V MAIN BLOK DIAGRAM, Revision: A, Pages: 1  
Drawing No. MM6 STANDARD LEVEL MAIN CIRCUIT DIAGRAM, VACON 100X MM6 - 208 - 500V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: A, Pages: 1  
Drawing No. MR10ED 500 V, STATEMENT OF TEST RESULTS, Revision: -, Pages: 1  
Drawing No. MR10ED 690 V, STATEMENT OF TEST RESULTS, Revision: -, Pages: 1  
Drawing No. MR12ED 500 V, STATEMENT OF TEST RESULTS, Revision: -, Pages: 1  
Drawing No. MR12ED 690 V, STATEMENT OF TEST RESULTS, Revision: -, Pages: 1  
Drawing No. MR4 DESIGN LEVEL MAIN CIRCUIT DIAGRAM, VACON 100 MR04 208-500 V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR4 Main Block Diagram, VACON 100 MR04 208-500 V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR5 6 DESIGN LEVEL, MR5 525-600V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. MR5 6 STANDARD LEVEL, MR5 525-600V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. MR5 Design Level Main Circuit Diagram, VACON 100 M505 208-500V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR5 Main Block Diagram, VACON 100 MR05 208-500V MAIN BLOCK DAIGRAM, Revision: B, Pages: 1  
Drawing No. MR6 6 7 DESIGN LEVEL, MR6 525-690V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. MR6 6 7 MAIN LEVEL, MR6 525-690V MAIN LEVEL, Revision: B, Pages: 1  
Drawing No. MR6 Design Level Main Circuit Diagram, VACON 100 MR06 208-500V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR6 Main Block Diagram, VACON 100 MR06 208-500V MAIN BLOCK DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR7 6 7 DESIGN LEVEL, MR7 525-690V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. MR7 6 7 STANDARD LEVEL, MR7 525-690V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. MR7 Standard Level Main Circuit Diagram, VACON 100 MR7 208-500V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR7 design level, VACON 100 MR7 208-500 V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: C, Pages: 1  
Drawing No. MR8 6 7 DESIGN LEVEL, 525-690V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. MR8 6 7 STANDARD LEVEL, 525-690V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. MR8 Standard Level Main Circuit Diagram, VACON 100 MR8 208-500 V STANDARD LEVEL MAIN CIRCUIT DIAGRAM, Revision: B, Pages: 1  
Drawing No. MR8 design level, VACON 100 MR8 208-500 V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: C, Pages: 1  
Drawing No. MR8ED 690 V, STATEMENT OF TEST REPORT, Revision: -, Pages: 1  
Drawing No. MR9 6 7 STANDARD LEVEL, 525-690V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. MR9 7 DESIGN LEVEL, 525-690V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. MR9 Standard Level Main Circuit Diagram, vacon 100 mr9 208-500v standard level main circuit diagram, Revision: C, Pages: 1  
Drawing No. MR9 design level, VACON 100 MR9 208-500V DESIGN LEVEL MAIN CIRCUIT DIAGRAM, Revision: D, Pages: 1  
Drawing No. MR9ED 690 V, STATEMENT OF TEST REPORT, Revision: -, Pages: 1  
Drawing No. Master\_list\_for\_Type\_Approval\_Vacon100\_series[1],  
Master\_list\_for\_Type\_Approval\_Vacon100\_series[1], Revision: -, Pages: 1  
Drawing No. TAD1+00/1, MR12 IP00 380-500V/525-690V MAIN LEVEL, Revision: A, Pages: 1  
Drawing No. TAD1+01/1, MR10 IP00 380-500V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. TAD1+02/1, MR10 IP00 380-500V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. TAD2+01/1, MR10 IP00 525-690V DESIGN LEVEL, Revision: B, Pages: 1  
Drawing No. TAD2+02/1, MR10 IP00 525-690V STANDARD LEVEL, Revision: B, Pages: 1  
Drawing No. VTT 06 ATEX 048X, EC TYPE EXAMINATION CERTIFICATE, Revision: -, Pages: 1



**VACON (CHINA) DRIVES CO. LTD. HAIYAN BRANCH**  
BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, P.R. CHINA  
JIAXING ZHEJIANG  
China 314300  
Telephone: 18121589808/021-6153000  
Fax: 02-61513100  
Email: leo.sun@danfoss.com  
Web: www.danfoss.cn

**Tier: 5 - Unit Certification Required** TC

Drawing No. Vacon-100-100-FLOW-Drive-Switch-Installation-instr, Revision: -, Pages: 1  
Drawing No. Vacon-100-Enclosed-Drives-Installation-Manual-DPD01666B-UK, Revision: -, Pages: 1  
Drawing No. Vacon-100-IP00-Drives-Installation-Manual-DPD01665B-UK, Revision: -, Pages: 1  
Drawing No. Vacon-100-Marine-Installation-Guide-DPD01773A-UK 11, Revision: -, Pages: 1  
Drawing No. Vacon-100-Wall-Mounted-Drives-Installation-Manual-DPD01711F-UK, Revision: -, Pages: 1  
Drawing No. Vacon-100-X-Graphical-Keypad-Installation-Manual-D, Revision: -, Pages: 1  
Drawing No. Vacon-100-X-Installation-Manual-DPD00534H-UK, Revision: -, Pages: 1  
Drawing No. Vacon-100-X-Mains-Switch-Installation-Manual-DPD00, Revision: -, Pages: 1  
Drawing No. Vacon-100-X-Optional-Heater-Arctic-Option-Installa, Revision: -, Pages: 1  
Drawing No. Vacon100, Vacon100, Revision: -, Pages: 1  
Drawing No. vacon-100-x-20-x-brochure-DPD01196B, Revision: -, Pages: 1  
Drawing No. 71395257, IP 66 test report for Vacon 100x, Revision: -, Pages: 6

**Terms of Validity:**

This Product Design Assessment (PDA) Certificate 15-LD1432892-1-PDA-DUP, dated 09/May/2016 remains valid until 19/Jan/2021 or until the Rules or specifications used in the assessment are revised (whichever occurs first).

This PDA is intended for a product to be installed on an ABS classed vessel, MODU or facility which is in existence or under contract for construction on the date of the ABS Rules or specifications used to evaluate the Product.

Use of the Product on an ABS classed vessel, MODU or facility which is contracted after the validity date of the ABS Rules and specifications used to evaluate the Product, will require re-evaluation of the PDA.

Use of the Product for non ABS classed vessels, MODUs or facilities is to be to an agreement between the manufacturer and intended client.

**STANDARDS**

**ABS Rules:**

- Steel Vessels (2016): 1-1-4/7.7, 1-1-Appendix 3 & 4, 4-8-3/8, 4-9-8/Table 1
- Steel Vessels Under 90 Meters (295 Feet) in Length (2016): 1-1-4/7.7, 1-1-Appendix 3 & 4, 4-6-4/10, 4-7-2/Table 1
- Facilities on Offshore Installations (2016): 1-1-4/9.7, 1-1- Appendix 2 & 3
- Offshore Support Vessels (2016): 1-1-4/7.7, 1-1-Appendix 3 & 4, 4-8-3/8, 4-9-8/Table 1
- Mobile Offshore Drilling Units (2016): 1-1-4/9.7, 1-1-Appendix 3 & 4, 6-1-1/9, 6-1-1/13, 6-1-7/12, 13.5
- High-Speed Craft (2016): 1-1-4/11.9, 1-1-Appendix 2 & 3, 4-6-4/10, 4-7-9/Table 9
- Steel Vessels for Service on Rivers and Intracoastal Waterways (2016): 1-1-4/7.7, 1-1-Appendix 3 & 4; 4-5-4/10
- High Speed Crafts (2016): 1-1-4/11.9, 1-1- Appendix 2 & 3; 4-6-4/10, 4-7-9 Table 9
- Steel Barge Rules (2016): 1-1-4/7.9, 1-1-Appendix 3 & 4

**National:**

NA

**International:**

IEC 61800-5-1 Ed 2.0: 2007, IEC 61800-3 Ed 2.0: 2004  
EN 61800-5-2:2007, EN 61800-5-1:2007, EN 61800-3: 2004+A1:2012, EN 61000-6-2:2005, EN 62061:2005 +AC: 2010, EN 60204-1:2006+A1:2009+AC: 2010, EN ISO13849-1:2008+AC: 2009

**Government:**

NA

**VACON (CHINA) DRIVES CO. LTD. HAIYAN BRANCH**

BLOCK 6-7, NO. 339 NORTH XINQIAO ROAD, WUYUAN STREET, HAIYAN COUNTY, JIAXING CITY,  
ZHEJIANG PROVINCE, P.R. CHINA

JIAXING ZHEJIANG

China 314300

Telephone: 18121589808/021-6153000

Fax: 02-61513100

Email: leo.sun@danfoss.com

Web: www.danfoss.cn

**Tier: 5 - Unit Certification Required**

---

**EUMED:**

NA

**OTHERS:**

NA