









Type	Value
Max Weight	27 kg / 59.53 lb
IP Class	IP21/55/66
Nema Class	Type 1/12/4X



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]			FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A2	MATERIAL
						FINISH
						DESCRIPTION
CHANGED						MCAD B2 IP66
DESIGNED	DANFOSS	27-11-2015				DRAWING NUMBER
CHECKED						MCAD-B2-IP66
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.						REV 001
						MODEL
						MCAD-B2-IP66
						SHEET 1 OF 1