





Type	Value
Max Weight	65 kg / 143 lb
IP Class	IP21
Nema Class	Type 1




DETAIL C
SCALE 1:2



DETAIL B
SCALE 1:1




DETAIL A
SCALE 1:1



COOLING CLEARANCE

AIR SPACE INLET




AIR
OUTLET


SEE DETAIL C

AIR
INLET

SEE DETAIL A




SEE DETAIL B



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

● CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1 MM (0,4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)			FIRST ANGLE PROJECTION	SCALE	SIZE	MATERIAL
				1:10	A3	
			FINISH			
			DESCRIPTION		MCAD FC C2 IP21 WO DISCONNECT	
CHANGED						
DESIGNED	Danfoss	2015-04-23				
CHECKED						
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER		REV	
			MCAD-FC-C2-IP21-WO-DISCONNECT		P1	
			MODEL		SHEET	
			C2-CUSTOMER-DRAWING		1 OF 2	



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
 SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL
 REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD-FC-C2-IP21-WO-DISCONNECT	P1
MODEL	SHEET
C2-CUSTOMER-DRAWING	2 OF 2