





ITEM	PART NUMBER	QTY	COMMENTS
1	70CMC13212.01	1	
2	132a0822_70CMC13213	1	
3	TPS-3MM-8	2	



SCALE 0.300



- NOTES:
- BEND RELIEFS TO BE MAXIMUM 1.5 TIMES THE MATERIAL THICKNESS, UNLESS NOTED.
 - BURR ALLOWABLE TO 15 PERCENT OF MATERIAL THICKNESS.
 - INSIDE BEND RADII TO BE EQUAL TO THE MATERIAL THICKNESS, UNLESS NOTED.

- ⊕ CRITICAL CHARACTERISTICS
 - ▽ KEY CHARACTERISTICS
 - INSPECTION
- MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

UNLESS OTHERWISE SPECIFIED INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS .X±0.4 .XX±0.20 ≤ ±1.0		THIRD ANGLE PROJECTION	SCALE 0.400	SIZE A2	MATERIAL DX51D+Z275MAC GALV. STEEL / EN10327; S=1.5
— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP				DESCRIPTION FAB_BRKT_DX51D_P7023_GLAND_PLATE - 1P54-UL_2XAAF	
CHANGED				DRAWING NUMBER 132a0822_70CMC13213	REV 001
DESIGNED	AP 12/08/17			MODEL 132a0822_70CMC13213	SHEET 1 OF 1
CHECKED		CONFIDENTIAL: PROPERTY OF DANFOSS A/S NØRDBØRG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			